

High Definition VideoScope Inspection Camera Kits

Narrow diameter cameras with 5.7" High Definition Color LCD* Monitor

Deliver high image resolution on large color display where images and videos can be stored on SD memory card (included)

Features:

- Model HDV610 kit HDV600 VideoScope and 5.5mm diameter camera head with 1m flexible cable Model HDV620 kit - HDV600 VideoScope and 5.8mm diameter camera head with 1m semi-rigid cable
- 5.7" color LCD* TFT with high definition 640 x 480 VGA pixel resolution
- Mini, high-resolution water-proof (IP57) camera head
- Rugged oil/chemical resistant and water/drop proof housing (IP67/2m)
- · Non-slip ergonomic handles for ambidextrous use
- SD memory card included to store >15,000 images
- Video recording (up to 4 hours) with Voice annotation
- · AV output for viewing images and video directly on a monitor
- Video and images can be transferred to a PC via the SD card or USB output
- An optional wireless transmitter (HDV-WTX) connects to your camera cable and allows you to transmit video up to 100ft (30m) from the measurement point to your monitor



A. Camera with 4 built-in bright LED lights illuminate dark areas. B. HDV-WTX — Optional Wireless Transmitter

- transmits video to the main display from tight or hard to reach places up to 100ft (30m) away
- C. Optional Articulating (6mm diameter) camera probes adjust up to 240° viewing angle (see below for ordering)

Ordering Information:

HDV610	High	Definition	VideoScope	Kit (5.5mm	diameter/1m	Flexible Ca	ble)
HDV620	High	Definition	VideoScope	Kit (5.8mm	diameter/1m	Semi-Rigid	Cable)

Video Inspector Monitor (order camera head separately from accessories listed below) HDV600High Definition VideoScope (Monitor and hard carrying case only)

Ontional camera accessories

HDV-TX16mm Articulating VideoScope Camera Head with Macro lens and 1m Semi-Rigid Cable
HDV-WTX16mm Wireless Articulating VideoScope Camera Head w/Macro lens & 1m Semi-Rigid Cable
HDV-TX2
HDV-WTX2
HDV-4CAM-1FM4mm VideoScope Camera Head with Macro lens and 1m Flexible Cable
HDV-4CAM-5FM4mm VideoScope Camera Head with Macro lens and 5m Flexible Cable
HDV-5CAM-1FM5.5mm VideoScope Camera Head with Macro lens and 1m Flexible Cable
HDV-5CAM-3F5.5mm VideoScope Camera Head with long depth of field and 3m Flexible Cable
HDV-5CAM-3FM5.5mm VideoScope Camera Head with Macro lens and 3m Flexible Cable
HDV-5CAM-30FM5.5mm VideoScope Camera Head with Macro lens and 30m Flexible Cable
HDV-5CAM-10F5.5mm VideoScope Camera Head with long depth of field and 10m Flexible Cable
HDV-5CAM-1R5.8mm VideoScope Camera Head with long depth of field and 1m Semi-Rigid Cable
HDV-5CAM-1RM5.8mm VideoScope Camera Head with Macro lens and 1m Semi-Rigid Cable
HDV-5CAM-3R5.8mm VideoScope Camera Head with long depth of field & 3m Semi-Rigid Cable
HDV-5CAM-3RM5.8mm VideoScope Camera Head with Macro lens and 3m Semi-Rigid Cable
HDV-25CAM-10G25mm VideoScope Camera Head with long depth of field and 10m Fiberglass Cable
HDV-25CAM-30G25mm VideoScope Camera Head with long depth of field and 30m Fiberglass Cable
HDV-WTXWireless Transmitter
HDV-PCSpare Patch Cable for HDV Series
ADPTR-HDV
BRD10Wireless USB Video Receiver



Specifications


Camera				
Minimum Focus distance	2.36" (60mm); macro: 0.59" (15mm)			
Field of View	65°			
Shaft diameter	HDV610: 0.22" (5.5mm)			
	HDV620: 0.23" (5.8mm)			
Working length	39" (1m)			
Borescope				
*LCD Color TFT Display	5.7" (14.5cm) size;			
	5.3" (13.5cm) viewable			
Pixels	640 x 480 VGA pixel resolution			
	(320 x 240 for 4mm camera)			
Frame Rate	30 fps frame rate (NTSC & PAL)			
SD Card	2GB SD memory card included			
	(supports up to 32GB SD storage)			
Operating	up to 4 hours AVI video			

HDV610 & HDV620 kits include:

 VideoScope HDV600, SD memory card, handset with camera probe and 1m cable (Probe accessories: magnet, 45° mirror, and anti-snag tip), 3.7V rechargable Li-Polymer battery, patch cable, Universal AC adapter (110-240V, four plugs), USB and AV cables, and hard carrying case

Applications:

- Industrial Processing & Manufacturing
- Heavy Equipment
- HVAC/Boilers
- Aerospace
- Government & Security
- Insurance



• Mining and Aggregate

Aviation AOG and FBO

 Building Inspection & Commissioning

· PetroChem/Refineries

Infrastructure

Power Generation



spool as shown on the left.

