



## GENERAL PRODUCT SPECIFICATION

Item No.      AW430

Date	16-6-2017	Replaces	4-11-11	No. Pages	1
------	-----------	----------	---------	-----------	---

### Product Description:

Style	SOC
Item Size (each)	7.6 cm dia x 122 cm long
Color	Gray with black logo printing
Composition	Polypropylene >98%, Surfactant < 1.0%, color pigment < 1.0 %
Structure	<u>Sorbent fill:</u> Micro-fibrous meltblown polypropylene (2-10 micron diameters) <u>Outer covering:</u> Spunbond polypropylene nonwoven (15-30 micron dia. fiber)
Technology	Meltblown + Spunbond + Sealed or Enclosed Ends
Absorbency	<b>Hydrophilic + Oleophilic</b>

**Intended Application**      Chemical Resistant "Universal" Sorbent Sock for Spills of Water Base, Oil Base, or Solvent Base Liquids

**Absorbency Capacity**      106 l per bale (saturated; medium viscosity- 9x)

### Packaging Description:

Package configuration	Case	Pkg. Weight	11.3 kg (10.2kg)
Items per Package	30 SOCS/Case	Pkg. Dimensions (approx.)	65 cm x 43 cm x 54 cm (H)
Container type	Carton		

### Physical Properties:

<u>Parameter</u>	<u>SPC Test Method</u>	<u>Units</u>	<u>Nominal</u>	<u>(+/-)Tolerance</u>
SOC Weight	Gravimetric	kg	0.36	0.09
Absorbency** (med. oil)	SPCTM-012B	gL/gS	9	8-min.
Color	Visual	-----	Gray	per standard

**The above properties are "nominal" values used for PROCESS CONTROL when the product is produced and/or inspected. Performance "nominals" may vary depending upon the specific application, and/or the environment being applied, stored, or shipped.**

**\*\* The "Absorbency" Spec and "SPCTM012" test method is based on the protocol of ASTM F726, using SAE20 non-detergent as the Oil Type, medium viscosity.**

<b>Attributes</b>	Product will be free of foreign material contamination, rips, holes, and tears.
<b>Labeling</b>	Each package to be clearly labeled with Company Name, Address, Item No., Date, and/or Package Code (Bar Code).
<b>Certification</b>	Make no changes in basic process or composition without notifying customer. Claims for non-conformance of goods must be made within 60-days of delivery.