



Electromagnetic protection braided sleeving for hybrid automobiles

Helagaine HEGEMIP-HY

Helagaine HEGEMIP-HY provides electromagnetic protection in hybrid automobiles.

Features and benefits

- Excellent electromagnetic protection
- Extremely flexible, expandable and easy to apply
- No kinks or ruptures even when bent at sharp angles
- Superior abrasion protection
- Special copper alloy for enhanced protection against salt spray
- Particularly suitable for applications with restricted space or requiring movement
- Inner disposable tube protects sleeve from deformation and allows for easy insertion of cables
- Fulfils the requirements of IEC CISPR25 for radio disturbances in vehicles, boats and engines



HEGEMIP-HY braided sleeving: EMI protection for hybrid automobiles.

MATERIAL	Polyester (PET), Tin Plated copper (SNCU)
Operating Temperature	-40 °C to +150 °C
EMI requirements	10 kHz to 1 GHz according to CISPR25 (DIN VDE 0879-2)
Flammability	UL 94 V2, FMVSS 302



TYPE	Ø (D)	Bundle Ø min.	Bundle Ø max.	Colour	Weight	Reel Length	Article-No.
HEGEMIP-HY20	20	19	27	Orange (OG)	72 g/m	50 m	173-02001
HEGEMIP-HY30	30	25	35	Orange (OG)	101 g/m	50 m	173-03000
HEGEMIP-HY35	35	30	40	Orange (OG)	120 g/m	50 m	173-03501
HEGEMIP-HY40	40	30	50	Orange (OG)	180 g/m	50 m	173-04000
HEGEMIP-HY50	50	40	60	Orange (OG)	193 g/m	50 m	173-05000

All dimensions in mm. Subject to technical changes.
Cuts in any lengths. Minimum Order Quantity (MOQ) may differ from package content.

