



GENERAL PRODUCT SPECIFICATION

Item No.	MRO200-E
----------	----------

Date	16-6-2017	Replaces	24-09-14	No. Pages	1
------	-----------	----------	----------	-----------	---

Product Description:

Style	Pads ; perforated on centerline for dividing in half for smaller applications
Item Size (each)	41 cm x 51 cm
Color	Gray
Composition	Polypropylene >98%, Surfactant < 1.0%, color pigment < 1.0 %
Structure	96% natural white meltblown nonwoven fibers(<10 microns) 4% white spunbond nonwoven coverstock(<15-30 microns)
Technology	Meltblown + spunbond
Absorbency	Universal (Hydrophilic + Oleophilic)
Bonding	Bonded (staggered pattern) + Mechanical entanglement

Intended Application	Low -Lint Chemical Resistant Sorbent for Water, Oil, or Solvent Base Liquids
----------------------	--

Absorbency Capacity	159 l per bale (saturated; medium viscosity-16x)
---------------------	--

Packaging Description:

Package configuration	1-Case	Pkg. Weight	9.5 kg (8.6 kg)
Items per Package	200-Pads/Case	Pkg. Dimensions	53 cm x 43 cm x 54 cm (H)
Container type	Carton		

Physical Properties:

Parameter	SPC Test Method	Units	Nominal	(+/-)Tolerance
Basis Weight	SPCTM-002A	G/M2	205	20
Caliper	SPCTM-020	mm	3.3	0.3
Absorbency** (med. Oil)	SPCTM-004B	gL/gS	16	1.6
Tensile Strength	SPCTM-007	daN	20	2
Color	Visual	-----	Gray	per standard

The above properties are “nominal” values used for **PROCESS CONTROL** when the product is produced and/or inspected. Performance “nominals” may vary depending upon the specific application, and/or the environment being applied, stored, or shipped.

**** The "Absorbency" Spec and "SPCTM004" test method is based on the protocol of ASTM F726, using SAE20 non-detergent as the Oil Type, medium viscosity.**

Attributes	Product will be free of foreign material contamination, rips, holes, and tears.
Labeling	Each package to be clearly labeled with Company Name, Address, Item No., Date, and/or Package Code (Bar Code).
Certification	Make no changes in basic process or composition without notifying customer. Claims for non-conformance of goods must be made within 60-days of delivery.