


ENERGIZER 10 size - Mercury Free





Industry Standard Dimensions



Typical Discharge Characteristics

0

ANSI/IEC Industry Standards / Hearing Aid High Drain (5/1.5 mA .1S/1H59M 59.9S 12H at 21C)



Specifications

Chemical System: Zinc Air (Zn/O₂)

Tab Color: Yellow

Designation: ANSI-7005ZD, IEC-PR70

Nominal Voltage: 1.4 Volts

Typical Capacity: 89 mAh (to 1.05 volts) (IEC-STD at 5/1 at 21°C)

Typical Weight: 0.32 grams (0.01 oz.)

Typical Volume: 0.08 cubic centimeters (0.005 cubic inch)

Typical Discharge Characteristics

(3/.7 mA .1S/1H59M 59.9S 12H at 21C)



Typical Discharge Characteristics

IEC Industry Standards / Hearing Aid Standard (5/1 mA .1S/1H59M 59.9S 12H at 21C)



Important Notice

This data sheet contains typical information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Form No. 10GL0118 Page 1 of 1