

# KERN HCB 0.5T-3

# KERN

Handy hanging scale for higher loads



## Construction

Dimension housing (W×D×H)	82×43×153 mm
Dimensions housing - width (A)	82 mm
Dimensions housing - depth (B)	43 mm
Dimensions - total height/total length (D)	153 mm
Dimensions - inner length (E)	117 mm
Dimensions loop/top - hole diameter (F)	16 mm
Dimensions hook/bottom - hole diameter (G)	16 mm
Dimensions loop/top - thickness (H)	4 mm
Dimensions hook/bottom - thickness (I)	4 mm
Material housing	plastic
Material display housing	Plastics
Material suspension	stainless steel
Material load cell(s)	aluminium
Load cells - number	1

## Functions

Number of keys for operation	3
Auto-off interval(s) in battery mode/rechargeable battery mode	off 4 min
Tare function	manual (multi)
Hold function	✓
Underfloor weighing	None
IP protection - load cell	no IP protection

## Power Supply

Supplied plug-in power supply	Battery
Battery	3×1.5 V AA
Battery operating time	300 h

## Environmental conditions

Humidity of environment [Max]	80 %
Ambient temperature [Min]	5 °C
Ambient temperature [Max]	35 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Shipping method	Parcel service
Dimensions packaging (W×D×H)	152×215×86 mm
Net weight approx.	0,40 kg
Gross weight approx.	0,70 kg

## Category

Brand	KERN
Product category	Industrial scales
Product group	Hanging balances

## Measuring System

Readability [d]	1000 g
Weighing capacity [Max]	500 kg
Eccentric/Off-centre loading is not possible	✓
Tolerance (% of [Max])	0,5%
Reproducibility	1 kg
Linearity	± 2 kg
Weighing system	Strain gauge
Resolution	500
Units	kg lb N
Default unit	kg
Stabilization time	2 s
Warm-up time	10 min
Adjustment options	Adjusting with external weight
Recommended adjusting weight	200 kg (M1)
Possible calibration points	200 kg
Loadcell type	aluminium
Internal measuring frequency	5 Hz

## Approval

CE mark	✓
---------	---

## Display

Display digit height	12 mm
----------------------	-------

# KERN HCB 0.5T-3



Handy hanging scale for higher loads

## Services (optional)

Article number for adjustment at the location of installation	961-250
Article number for DAkkS calibration	963-130H
Article number for certificate of conformity (verification)	969-517

## Piktogramme

### STANDARD



### OPTION

