

Brother HLJ6010DWRE1 inkjet printer Colour 1200 x 4800 DPI A3 Wi-Fi

Brand : Brother

Product code: HLJ6010DWRE1

Product name : HLJ6010DWRE1

Brother HLJ6010DWRE1. Colour, Number of print cartridges: 4, Maximum duty cycle: 3500 pages per month. Maximum resolution: 1200 x 4800 DPI. Maximum ISO A-series paper size: A3. Print speed (black, normal quality, A4/US Letter): 30 ppm. Duplex printing. Wi-Fi. Product colour: White



Features		Network	
Duplex printing *	✓	Near Field Communication (NFC)	✓
Duplex printing mode	Auto	Security algorithms	802.11+ RADIUS, APOP, EAP-FAST, EAP-MD5, EAP-TLS, EAP-TTLS, HTTPS, IPPS, PEAP, SMTP-AUTH, SNMPv3, SSL/TLS, WPA-PSK, WPA2-PSK, WPA3-SAE
Page description languages *	BR-Script 3, PCL 6, PDF 1.7, XPS	Mobile printing technologies	Apple AirPrint, Brother iPrint & Scan, Mopria Print Service
Printing colours *	Black, Cyan, Magenta	Performance	
Colour *	✓	Internal memory *	512 MB
Maximum duty cycle *	3500 pages per month	Sound pressure level (printing)	53 dB
Number of print cartridges *	4	Design	
Printing		Market positioning *	Home & office
Maximum resolution *	1200 x 4800 DPI	Product colour *	White
Print speed (black, normal quality, A4/US Letter) *	30 ppm	Built-in display *	✓
Print speed (colour, normal quality, A4/US Letter)	21 ppm	Display diagonal	17,3 cm (6.8")
Time to first page (black, normal)	4,6 s	Control type	Touch
Input & output capacity		Power	
Total number of input trays *	2	Power consumption (printing) *	24 W
Total input capacity *	250 sheets	Power consumption (ready)	5 W
Total output capacity *	100 sheets	System requirements	
Paper handling		Windows operating systems supported	Windows 10, Windows 7, Windows 8
Maximum ISO A-series paper size *	A3	Mac operating systems supported	Mac OS X 10.14 Mojave, Mac OS X 10.15 Catalina, Mac OS X 10.15.3 Catalina
Paper tray media types *	Photo paper, Plain paper, Recycled paper	Linux operating systems supported	✓
ISO A-series sizes (A0...A9) *	A3, A4, A5, A6	Server operating systems supported	Windows Server 2008, Windows Server 2008 R2, Windows Server 2012, Windows Server 2016, Windows Server 2019
ISO C-series sizes (C0...C9)	C5	Weight & dimensions	
Non-ISO print media sizes	Index card, Legal	Width	681 mm
Envelopes sizes	DL, Monarch	Depth	561 mm
Photo paper sizes	9x13, 10x15, 13x18	Height	493 mm
Paper tray media weight	64 - 220 g/m ²	Weight	19,6 kg
Ports & interfaces		Packaging data	
USB port *	✓	Cartridge(s) included	✓
USB 2.0 ports quantity	1	Included cartridge capacity (black)	6000 pages
Direct printing	✓	Included cartridge capacity (CMY)	5000 pages
Network		Package width	576 mm
Ethernet LAN *	✓	Package depth	477 mm
Wi-Fi *	✓	Package height	315 mm
Wi-Fi Direct *	✓	Package weight	22,6 kg
Wi-Fi standards	802.11a, 802.11b, 802.11g, Wi-Fi 4 (802.11n)		



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.