



### Flame-retardant, high-expansion polyester braided sleeving

#### Helagaine HEGPETFRX

Helagaine HEGPETFRX is especially suitable for areas wherever fire protection is important as well as a higher expansion ratio of the braided sleeve. Helagaine HEGPETFRX offers superior cable protection for machine tools, robotics and automatic equipment.

#### Features and benefits

- Made of sturdy polyester
- Self-extinguishing
- Highly flexible
- High rate of expansion
- Easy to apply over irregular shapes
- Good abrasion resistance



Helagaine HEGPETFRX.

<b>MATERIAL</b>	Polyester (PET)
<b>Operating Temperature</b>	-50 °C to +150 °C
<b>Melting Point</b>	+250 °C
<b>Flammability</b>	FMVSS 302, Type B, UL 1441 VW-1



TYPE	Bundle Ø min.	Bundle Ø max.	Colour	Reel Length	Tools	Article-No.
HEGPETFRX03	2	6	Black with Grey Identification Yarn (BKIDGY)	200 m	45	170-81100
HEGPETFRX06	3	10	Black with Grey Identification Yarn (BKIDGY)	200 m	45	170-81101
HEGPETFRX09	5	16	Black with Grey Identification Yarn (BKIDGY)	100 m	45	170-81102
HEGPETFRX12	6	19	Black with Grey Identification Yarn (BKIDGY)	100 m	45	170-81103
HEGPETFRX20	12	32	Black with Grey Identification Yarn (BKIDGY)	100 m	45	170-81104
HEGPETFRX30	19	45	Black with Grey Identification Yarn (BKIDGY)	50 m	45	170-81105
HEGPETFRX40	32	70	Black with Grey Identification Yarn (BKIDGY)	50 m	45	170-81106
HEGPETFRX50	38	76	Black with Grey Identification Yarn (BKIDGY)	50 m	45	170-81107

All dimensions in mm. Subject to technical changes.

Recommended Tools	
	45 HSG0
	570

For more information on toolings please refer to the Application Tooling chapter.



For product specific approvals and specifications please refer to the Appendix.



Add items to your watchlist!

[www.HT.click/49-351](http://www.HT.click/49-351)

