



Vinyl Electrical Tapes – Premium Vinyl Electrical Tape

HelaTape Flex 1000+

Features and Benefits

- All-weather, highly flexible, professional grade, self-adhesive vinyl electrical tape
- Excellent performance and durability over wide temperature range from -18°C to +105°C according to CSA C22.2
- VDE approved according to IEC 60454-3-1-7/F-PVCP/90
- Used for insulation, protection, fixing, maintenance, colour coding and more
- Pressure sensitive high quality rubber based adhesive
- Performs continuously at low temperature environment
- Excellent resistance to abrasion, moisture, chemicals, corrosion and UV exposure
- Primary electrical insulation for all wire and cable splices up to 1 kV
- Protective jacketing for low, medium and high voltage splices and repairs
- Flame retardant according to UL 510 Standard
- For indoor and outdoor applications
- Size 19 mm x 20 m is single packed in a plastic can, only 710-10601 comes in a pack of 10 pcs.



HelaTape Flex 1000+ provides excellent low temperature performance.

MATERIAL	Polyvinylchloride (PVC)
Dielectric Strength	45 kV/mm
Adhesion to Steel	3.0 N/10 mm
Adhesion to Backing	2.5 N/10 mm
Elongation at break	300 %
Breaking Strength	35 N/10 mm
Operating Temperature	-18 °C to +105 °C



TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-FLEX1000+19x6	0.18	19.0	6.0 m	Black (BK)	710-10600
HTAPE-FLEX1000+19x20 PACK	0.18	19.0	20.0 m	Black (BK)	710-10601
HTAPE-FLEX1000+19x20	0.18	19.0	20.0 m	Black (BK)	710-10602
	0.18	19.0	20.0 m	Blue (BU)	710-10603
	0.18	19.0	20.0 m	Brown (BN)	710-10608
	0.18	19.0	20.0 m	Green (GN)	710-10606
	0.18	19.0	20.0 m	Green-Yellow (GNYE)	710-10612
	0.18	19.0	20.0 m	Grey (GY)	710-10609
	0.18	19.0	20.0 m	Red (RD)	710-10604
	0.18	19.0	20.0 m	White (WH)	710-10607
	0.18	19.0	20.0 m	Yellow (YE)	710-10605
HTAPE-FLEX1000+19x33	0.18	19.0	33.0 m	Black (BK)	710-10610
HTAPE-FLEX1000+50x33	0.18	50.0	33.0 m	Black (BK)	710-10611

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.



Please note! Not all products listed on this page may have this approval. Please check our website for latest approvals.