



Self-amalgamating Tapes – Vinyl Mastic Tape

HelaTape Power 670 VM

Features and Benefits

- Easy to apply vinyl mastic tape
- Self-adhesive application - without stretching
- Mastic layer is very sticky and provides excellent moisture sealing
- Vinyl top layer provides additional protection
- Performs continuously at low temperature environment
- Primary insulation up to 1 kV
- Compatible with all extruded cable insulations
- UV and weather resistant



HelaTape Power 670 provides additional vinyl film protection to the mastic compound.

MATERIAL	Polyvinylchloride (PVC), Isobutene-Isoprene-Rubber (butyl rubber) (IIR)
Operating Temperature	+80 °C
Intermittent Operating Temperature	+95 °C
Water Absorption	0.9 %
Tensile Strength	16 N/mm ²
Elongation at break	200 %
Volume Resistance	10 ¹² Ω cm
Dielectric Strength	19.7 kV/mm



TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-POWER670-VM	1.20	100.0	3.0 m	Black (BK)	711-00304

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.