




## Cable glands, degree of protection IP 66 (750 °C)


	<h3>ASS 20</h3> <ul style="list-style-type: none"> <li>• Cable glands</li> <li>• for knockouts M 20</li> </ul>		
---	--	---	---

- sealing range: Ø 5-13.5 mm
- ISO thread M 20 x 1.5
- bore-hole: Ø 20.3 mm
- wall thickness up to 3 mm
- with strain relief and locknut
- for indoor (normal environment and/or protected outdoor) and outdoor installation (harsh environment and/or outdoor)
- ambient temperature - 25 °C to + 55 °C
- glow wire test IEC 60695-2: 960 °C
- colour: black, RAL 9005
- degree of protection: IP 66 / IP 67 / IP 69

tightening torque	4,0 Nm
width across flats of cable glands	24 mm
Dimension across corners of cable glands Ø	26,5 mm
width across flats of nut	27 mm
dimension across corners Ø	30,2 mm
material	PA (Polyamide)
weight	0,012 kg
glow wire test	IEC 60695-2-11 960°C
in accordance with	DIN EN 62444
in accordance with	DNV GL - Certificate No: TAE000041H

## Drawings

Dimension drawing



## Operating and ambient conditions

Application area	Suitable for for outdoor installation (harsh environment and/or outdoor).
------------------	---

Resistant to occasional cleaning procedures (direct jet)	Resistance to occasional cleaning procedures (direct jet) with high-pressure cleaner without cleaning additives, water pressure: max 100 bar, water temperature: max 80 °C, distance ≥ 0.15 m, in accordance with DIN EN 60529:2014-09 (IEC 60529:2013) = IP 69.
Ambient temperature	Average value over 24 hours + 55 °C maximum back-up fuse: + 70 °C Minimum value - 25 °C
Fire protection in the event of internal faults	Demands placed on electrical devices from standards and laws Minimum requirements - Glow wire test in accordance with IEC 60695-2-11: - 650° C for boxes and cable glands
Burning behaviour	Glow wire test IEC 60695-2-11: 960 °C UL Subject 94: V-0 flame-retardant self-extinguishing
Toxic behaviour	halogen-free silicone-free "halogen-free" in accordance with the examination of the cables and insulated wires - corrosiveness of fumes - as per IEC 60754-2
Note:	For material properties see technical data.