

HNS 25 W G13

PURITEC HNS UV-C | UV-C lamps for purification



Areas of application

- Efficient disinfecting of air, water and surfaces

Product family benefits

- Effective and environment-friendly disinfection without chemicals
- Low mercury content
- Long lifetime due to specific coating
- Ozone-free

Product family features

- Dominant wavelength: 254 nm (OFR version)



Product datasheet

Technical data

Product information

Order reference	HNS 25W G13
-----------------	-------------


Electrical data

Nominal voltage	46.0 V
Lamp voltage	46 V
Construction voltage	46.00 V
Nominal current	0.6 A
Lamp current	0.6 A
Nominal wattage	25.00 W

Photometrical data

Luminous intensity	7800 cd
Radiated power 200...280 nm (UVC)	6.9 W

Dimensions & weight



Diameter	26.0 mm
Length	438.0 mm

Lifespan

Lifespan	9000 h
----------	--------

Additional product data

Base (standard designation)	G13
-----------------------------	-----

Capabilities

Burning position	Any
------------------	-----

Product datasheet

Country specific categorizations

Order reference	HNS 25W G13
------------------------	-------------

Country specific information

Product code	METEL-Code	SEG-No.	STK number	UK Org
4008321398857	-	-	4834804	-
4008321398857	-	-	4834804	-
4008321398871	-	-	4834804	-

HNS 25 W G13

PURITEC HNS UV-C | UV-C lamps for purification

Product name	Product name ECG	EAN
HNS 25 W G13	QTP5 1x80	4008321329059

Product datasheet

Safety advice

PURITEC germicidal lamps emit high-intensity UV radiation that can cause sunburn and conjunctivitis. The skin and eyes must therefore not be exposed to direct or reflected unfiltered radiation.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321398857	HNS 25 W G13	Sleeves 1	455 mm x 27 mm x 27 mm	0.33 dm ³	85.00 g
4008321398864	HNS 25 W G13	Shipping carton box 20	471 mm x 132 mm x 153 mm	9.51 dm ³	1685.00 g
4008321398871	HNS 25 W G13	Shipping carton box 200	685 mm x 332 mm x 488 mm	110.98 dm ³	19710.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.
