




Vinyl Electrical Tapes – Premium Heavy Duty Vinyl Electrical Tape

HelaTape Flex 2000+

Features and Benefits

- All-weather, highly flexible, professional grade, self-adhesive vinyl electrical tape with higher thickness for more mechanical and electrical protection
- Excellent performance and durability over wide temperature range from -18 °C to +105 °C according to CSA C22.2
- Pressure sensitive and aggressive high quality rubber based adhesive
- Performs continuously at low temperature environment
- Flame retardant according to UL 510 Standard
- Excellent resistance to abrasion, moisture, chemicals, corrosion and UV exposure
- Primary electrical insulation for all wire and cable splices up to 1 kV



HelaTape Flex 2000+ is the best choice for professional installation.

MATERIAL	Polyvinylchloride (PVC)
Dielectric Strength	48 kV/mm
Adhesion to Steel	2.8 N/10 mm
Adhesion to Backing	2.4 N/10 mm
Elongation at break	300 %
Breaking Strength	40 N/10 mm
Operating Temperature	-18 °C to +105 °C

RoHS ✓

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-FLEX2000+19x20	0.21	19.0	20.0 m	Black (BK)	710-10701
HTAPE-FLEX2000+38x20	0.21	38.0	20.0 m	Black (BK)	710-10705

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.