



Self-amalgamating Tapes – Silicone Rubber Tape

HelaTape Power 800

Features and Benefits

- Self-amalgamating and self-cleaning, chemically cross-linked silicone rubber tape
- Triangular cross-section with centre line for precise half-overlapping
- Resistant to creepage and surface erosion
- Fuses into solid mass after application
- Weather, UV and oil resistant
- Recommended use for high temperature silicone insulated cables and outdoor machinery and transformers



HelaTape Power 800 is a silicone rubber tape with triangular cross-section.

| | |
|------------------------------|-----------------------|
| MATERIAL | Silicone (SI) |
| Operating Temperature | +180 °C |
| Tensile Strength | 7 N/mm ² |
| Elongation at break | 400 % |
| Volume Resistance | 10 ¹⁴ Ω cm |
| Dielectric Strength | 23.5 kV/mm |



| TYPE | Thickness (T) | Width (W) | Length (L) | Colour | Article-No. |
|----------------|---------------|-----------|------------|-----------|-------------|
| HTAPE-POWER800 | 0.51 | 25.0 | 9.1 m | Grey (GY) | 711-10400 |

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.