



### Self-amalgamating Tapes – High Voltage Rubber Tape

#### HelaTape Power 810

#### Features and benefits

- Self-amalgamating tape for insulating and jacketing splices up to 69 kV
- Halogen-free with outstanding corona, ozone and UV-resistance
- Ideal for sealing of terminations, electrical connections and cable jacket repair
- Void-free, electrically stable layering
- Protects e.g. bus bars against corrosion and contact
- Excellent moisture, corrosion and chemical resistance
- Compatible with all extruded cable insulations



HelaTape Power 810 for primary insulation up to 69 kV.

<b>MATERIAL</b>	Ethylene Propylene Rubber (EPR)
<b>Operating Temperature</b>	+90 °C
<b>Intermittent Operating Temperature</b>	+130 °C
<b>Water Absorption</b>	0.06 %
<b>Tensile Strength</b>	2.4 N/mm <sup>2</sup>
<b>Elongation at break</b>	750 %
<b>Volume Resistance</b>	10 <sup>16</sup> Ω cm
<b>Dielectric Strength</b>	30 kV/mm

HF ✓

RoHS ✓

TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-POWER810	0.76	19.0	9.1 m	Black (BK)	711-10401

All dimensions in mm. Subject to technical changes.  
Minimum Order Quantity (MOQ) may differ from package content.



Add items to your watchlist!  
[www.HT.click/49-407](http://www.HT.click/49-407)