



### General specifications

- Snap on fixing on rail 35mm EN 50022
- Heat sink and cover in black anodized aluminum profile
- Heating element consists of a self-regulating PTC resistor
- 3 cage clamp terminals for solid or fine stranded wires 0.5÷2.5mm<sup>2</sup> (20÷16 AWG)
- UL approval according to UL 508



► Quick electrical connection with cage clamp terminal

### Technical data

Model	A	B	Heating Power	Rated Voltage	Weight	Approvals
	mm	mm	W	V	Kg	
HTM045	138	40	45	110-240 V a.c./d.c.	0.5	CE; cURus;
HTM060	138	40	60	110-240 V a.c./d.c.	0.5	CE; cURus;
HTM080	188	65	80	110-240 V a.c./d.c.	0.65	CE; cURus;
HTM100	188	65	100	110-240 V a.c./d.c.	0.65	CE; cURus;
HTM150	238	90	150	110-240 V a.c./d.c.	0.84	CE; cURus;

### Technical specifications

