

# Charging cable Mode3 Typ2 32A 1ph 5m



Part number	08 91 409 0107 A0
Specification	Charging cable Mode3 Typ2 32A 1ph 5m
HARTING eCatalogue	https://b2b.harting.com/08914090107A0

Image is for illustration purposes only. Please refer to product description.

#### Identification

Element	Charging cable
Specification	Straight
Charging mode	Mode 3
Connector 1	Type 2 Female (Vehicle side)
Connector 2	Type 2 Male (infrastructure side)

#### Version

Cable length	5 m
Termination method	Crimp termination
Core structure	3x 6 mm² + 0.5 mm²
Number of phases	1
Number of contacts	5
Number of signal contacts	2
Number of power contacts	3
Contact configuration	Signal: CP, PP Power: L1, N, PE
Details	Also available with customer specific logo on request.

### Technical characteristics

Rated current (signal)	2 A
Rated voltage (signal)	30 V
Rated current (power)	32 A



#### Technical characteristics

Rated voltage (power)	250 V
Type of current	AC
Charging power	7.4 kW
Coding resistance	220 Ω between PE and PP
Ambient temperature	-30 +50 °C in operation -40 +80 °C storage/transport
Air pressure	≥540 hPa ≈ 5000 m
Insertion force	<100 N
Withdrawal force	<100 N
Mating cycles	≥10,000
Degree of protection acc. to IEC 60529	IP44 mated condition
Cable diameter	12.8 mm ± 0.4 mm
Minimum bending radius	9x Cable diameter (repeated bending)
Conductor resistance @ 20 °C	≤3.3 $\Omega$ /km @ 6 mm <sup>2</sup> ≤39 $\Omega$ /km @ 0.5 mm <sup>2</sup>

## Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Black
Material (cover)	Thermoplastic polyurethane (TPU)
Material (cable)	Thermoplastic polyurethane (TPU)
Colour (cable)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes



## Material properties

REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

## Specifications and approvals

Specifications	IEC 62196-2 IEC 62893
CE	Yes

#### Commercial data

Packaging size	1
Net weight	2.164 kg
Country of origin	Romania
European customs tariff number	85444991
eCl@ss	27144705 Charging cable E-Mobility