

M12 A-cod 5-pol st /st m /f PVC 5.00m



Image is for illustration purposes only. Please refer to product description.

Part number	C2 13 200 0000 0009
Specification	M12 A-cod 5-pol st /st m /f PVC 5.00m
HARTING eCatalogue	https://b2b.harting.com/C21320000000009

Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	M12 A-coding Male Straight Overmoulded
Connector 2	M12 A-coding Female Straight Overmoulded
Type of cable	Copper cable (round)

Version

Cable length	5 m
Number of cores	5
Core structure	5x 0.34 mm ²
Termination method	Crimp termination
Shielding	Unshielded
Coding	A-coding

Technical characteristics

Rated current	4 A
Rated voltage	60 V
Limiting temperature	-25 ... +80 °C moved -40 ... +80 °C unmoved



Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529 IP65 / IP67 mated condition

Cable diameter 5.3 mm

Material properties

Material (cable) PVC

Colour (cable) RAL 7040 (Window grey)

RoHS compliant

ELV status compliant

China RoHS e

REACH Annex XVII substances Not contained

REACH ANNEX XIV substances Not contained

REACH SVHC substances Not contained

California Proposition 65 substances Not contained

Specifications and approvals

Approvals CE

Commercial data

Packaging size 2

Country of origin Germany

European customs tariff number 85444290

GTIN 5713140512870

ETIM EC001855

eCl@ss 27060311 Assembled sensor actuator-line