

Cable Shears

- for cutting copper and aluminium single conductors as well as multiple stranded cables
- not suitable for steel wire and wire ropes
- precision ground, hardened blades
- clean and smooth cut without crushing and deformation
- less effort required due to favourable lever ratio and optimised cutting-edge geometry
- short design, length only 500 mm
- low weight
- guard prevents operators' fingers being pinched
- adjustable bolted joint
- Cutter head: vanadium electric steel, forged, oil-hardened
- Handles: aluminium tube, high-strength



Large cutting capacity: max. 27 mm dia. / 150 mm²



Article No.	EAN 4003773-	1000 V	Head	Handles	Cutting capacities			
					Ø mm	mm ²	AWG	mm
95 17 500	026785		polished	with dipped insulation, VDE-tested	27	150	5/0	500

Cable Shears

- for cutting copper and aluminium single conductors as well as multiple stranded cables
- not suitable for steel wire and wire ropes
- precision ground, hardened blades
- clean and smooth cut without crushing and deformation
- favourable lever ratio due to toggle lever
- guard prevents operators' fingers being pinched
- adjustable bolted joint
- bolted cutter head, replaceable
- cutter head: high-grade chrome vanadium electric steel, forged, oil-hardened
- Handles: steel tube



Article No.	EAN 4003773-	1000 V	Head	Handles	Cutting capacities			
					Ø mm	mm ²	AWG	mm
95 27 600	021797		polished	with dipped insulation, VDE-tested	27	150	5/0	600

95 29 600	021803	Spare cutter head for 95 21 600 / 95 27 600						
-----------	--------	---	--	--	--	--	--	--