



Technical Data

27.11.2023

Heat shrinkable tubing - PTFE
TFE2 - 2:1 shrink ratio

TFE2-14

Article Number 336-00319



Material: Polytetrafluoroethylene (PTFE)
Colour: Transparent (CL)

Supplied \varnothing D min.: 3.05 mm
Recov. \varnothing d max.: 1.83 mm
Wall (WT): 0.30 mm
Shrink Ratio: 2:1
Longitudinal Change After Shrinkage: -20% max.
Min. Shrink Temperature - °C: +330 °C

Operating Temperature : -65 °C to +260 °C

Test Method

Dielectric Strength: 40 kV/mm
Elongation at break: 500%

DIN 53481

RoHS ✓

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved