

# ICP402025PC-01

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V  
 Safety Circuit, Connector, **IEC62133 certified**

## Specifications

Renata Type	ICP402025
IEC Designation	ICP052128
Part Number	100644
Contact Method	Connector
Safety Circuit	Yes

Nominal Voltage	3.7 V
Nominal Capacity	155 mAh
Minimum Capacity	150 mAh ( 0.2C cut off 3.0 V at 20°C )

Internal Impedance < 400 mΩ / 30% SOC

Thickness ( t )	Max 4.3 mm
Length ( l )	Max 27.5 mm
Width ( w )	Max 20.5 mm
Weight	~ 4.0 g

## Charging Characteristic

Charging Characteristic	CC/CV – Constant Current / Constant Voltage
Voltage	4.2 V CV
Current Normal	0.5 C CC – 77.5 mA
Max. Charging Current	1.0 C CC – 155 mA
Temperature at Charging	0 °C .... 45 °C


## Discharge Characteristic

Cut off Voltage	3.0 V
Max Discharge Current	2.0 C – 310 mA ( for non continues discharge ) 1.0 C – 155 mA ( for continues discharge )
Temperature during Discharge	-20 °C ... 60 °C

Cycle Life at Room Temperature > 80% of minimum capacity after 500 cycles ( 0.5 C charge, 0.5 C discharge )

Storage Temperature -20 °C ... 45 °C  
 ( 0 °C ... 30 °C recommended in case of storage for more than 3 months)

## Dimensions



*Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.*