

ICP401230UPR

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V

Safety Circuit

Specifications

Renata Type	ICP401230
IEC Designation	ICP051331
Part Number	100642
Contact Method:	Wire AWG 30
Safety Circuit	Yes

Nominal Voltage	3.7 V
Nominal Capacity	130 mAh
Minimum Capacity	125 mAh (0.2C cut off 3.0 V at 20°C)
Internal Impedance	< 340 mΩ / 30% SOC

Thickness (t)	Max 4.5 mm
Length (l)	Max 31.0 mm
Width (w)	Max 12.7 mm
Weight	~ 3.5 g


Charging Characteristic	CC/CV – Constant Current / Constant Voltage
Voltage	4.2 V CV
Current Normal	0.5 C CC – 65 mA
Max. Charging Current	1.0 C CC – 130 mA
Temperature at Charging	0 °C 45 °C

Discharge Characteristic	
Cut off Voltage	3.0 V
Max discharge Current	2.0 C – 260 mA (for non continues discharge) 1.0 C – 130 mA (for continues discharge)
Temperature during Discharge	-20 °C ... 60 °C

Cycle Life at Room Temperature	> 80% of minimum capacity after 500 cycles (0.5 C charge, 0.5 C discharge)
--------------------------------	--

Storage Temperature	-20 °C ... 45 °C (0 °C ... 30 °C recommended in case of storage for more than 3 months)
---------------------	---

Dimensions



Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.

Rev. Li Ion ICP401230 – 17.07