

# ICP501022UPM

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V  
With Safety Circuit

## Specifications

Renata Type	ICP501022
IEC Designation	ICP061024
Part Number	100640
Contact:	Wire AWG 30
Safety Circuit	Yes

Nominal Voltage	3.7 V
Nominal Capacity	80 mAh
Minimum Capacity	75 mAh (0.2C cut off 3.0 V at 20°C)
Internal Impedance	< 460 mΩ / 30% SOC

Thickness ( t )	Max 5.5 mm
Length ( l )	Max 24.0 mm
Width ( w )	Max 10.0 mm
Weight	~ 2.6 g


<b>Charging Characteristic</b>	CC/CV – Constant Current / Constant Voltage
Voltage	4.2 V CV
Current Normal	0.5 C CC – 40 mA
Max. Charging Current	1.0 C CC – 80 mA
Temperature at Charging	0 °C .... 45 °C

<b>Discharge Characteristic</b>	
Cut off Voltage	3.0 V
Max Discharge Current	2.0 C – 160 mA ( for non continues discharge ) 1.0 C – 80 mA ( for continues discharge )
Temperature during Discharge	-20 °C ... 60 °C

Cycle Life at Room Temperature	> 80% of minimum capacity after 500 cycles ( 0.5 C charge, 0.5 C discharge )
--------------------------------	--

Storage Temperature	-20 °C ... 45 °C ( 0 °C ... 30 °C recommended in case of storage for more than 3 months)
---------------------	---

## Dimensions



*Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.*