

## ICP402035

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V

### Specifications

Renata Type	ICP402035
IEC Designation	ICP052136
Part Number	100645
Contact Method:	Tabs
Safety Circuit	Yes
Nominal Voltage	3.7 V
Nominal Capacity	195 mAh
Minimum Capacity	190 mAh ( 0.2C cut off 3.0 V at 20°C )
Internal Impedance	< 120 mΩ / 30% SOC

Thickness ( t )	Max 4.5 mm
Length ( l )	Max 36.0 mm
Width ( w )	Max 20.5 mm
Weight	~ 4.8 g

### Charging Characteristic

Voltage	CC/CV – Constant Current / Constant Voltage 4.2 V CV
Current Normal	0.5 C CC – 97.5 mA
Max. Charging Current	1.0 C CC – 195 mA
Temperature at Charging	0 °C .... 45 °C


### Discharge Characteristic

Cut off Voltage	3.0 V
Max Discharge Current	2.0 C – 390 mA ( for non continues discharge ) 1.0 C – 195 mA ( for continues discharge )
Temperature during Discharge	-20 °C ... 60 °C

Cycle Life at Room Temperature > 80% of minimum capacity after 500 cycles ( 0.5 C charge, 0.5 C discharge )

Storage Temperature -20 °C ... 45 °C  
( 0 °C ... 30 °C recommended in case of storage for more than 3 months)

### Dimensions



*Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.*