


ICP543759PMT

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V
With Safety Circuit, **IEC62133 certified**

Specifications

Renata Type	ICP543759
IEC Designation	ICP063861
Part Number	100652
Contact Method	Wire AWG 30
Safety Circuit	Yes
Nominal Voltage	3.7 V
Nominal Capacity	1320 mAh
Minimum Capacity	1260 mAh (0.2C cut off 3.0 V at 20°C)
Internal Impedance	< 280 mΩ / 30% SOC
Thickness (t)	Max 5.95 mm
Length (l)	Max 61 mm
Width (w)	Max 37.5 mm
Weight	~ 26 g
Charging Characteristic	CC/CV – Constant Current / Constant Voltage
Voltage	4.2 V CV
Current Normal	0.5 C CC – 660 mA
Max. Charging Current	1.0 C CC – 1320 mA
Temperature at Charging	0 °C 45 °C
Discharge Characteristic	
Cut off Voltage	3.0 V
Max Discharge Current	2.0 C – 2640 mA (for non continues discharge) 1.0 C – 1320 mA (for continues discharge)
Temperature during Discharge	-20 °C ... 60 °C
Cycle Life at Room Temperature	> 80% of minimum capacity after 500 cycles (0.5 C charge, 0.5 C discharge)
Storage Temperature	-20 °C ... 45 °C (0 °C ... 30 °C recommended in case of storage for more than 3 months)

Dimensions



Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.