

## ICP606168PRT

Rechargeable Lithium Ion Polymer Battery Pack 3.7 V  
Safety Circuit with NTC

### Specifications

Renata Type	ICP606168
IEC Designation	ICP076271
Part Number	100758
Contact:	Wire AWG 26
Safety Circuit	Yes with NTC

Nominal Voltage	3.7 V
Nominal Capacity	2800 mAh
Minimum Capacity	2700 mAh (0.2C cut off 3.0 V at 20°C)
Internal Impedance	< 200 mΩ / 30% SOC

Thickness ( t )	Max 6.7 mm
Length ( l )	Max 71.0 mm
Width ( w )	Max 62.0 mm
Weight	~ 70 g

### Charging Characteristic

Voltage	CC/CV – Constant Current / Constant Voltage 4.2 V CV
Current Normal	0.5 C CC – 1400 mA
Max. Charging Current	1.0 C CC – 2800 mA
Temperature at Charging	0 °C .... 45 °C

### Discharge Characteristic


Cut off Voltage	3.0 V
Max Discharge Current	0.8 C – 2240 mA ( for continues discharge )

Temperature during Discharge	-20 °C ... 60 °C
------------------------------	------------------

Cycle Life at Room Temperature	> 80% of minimum capacity after 300 cycles ( 0.5 C charge, 0.5 C discharge )
--------------------------------	--

Storage Temperature	-20 °C ... 45 °C ( 0 °C ... 30 °C recommended in case of storage for more than 3 months)
---------------------	---

### Dimensions



*Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.*