

## **ICP632136HPST**

Rechargeable Lithium Ion Polymer Battery Pack 3.8 V Safety Circuit, NTC

## **Specifications**

Renata Type ICP632136
IEC Designation ICP072240
Part Number 101030
Contact Method: Wire AWG 30
Safety Circuit Yes, incl. NTC

Nominal Voltage 3.8 V
Typical Capacity 520 mAh
Minimum Capacity 500 mAh

(0.2C cut off 3.0 V at

20°C)

Internal Impedance  $< 240 \text{ m}\Omega / 30\% \text{ SOC}$ 

 $\begin{array}{lll} \mbox{Thickness (t)} & \mbox{Max 6.95 mm (after 500 cycles)} \\ \mbox{Lenghth (I)} & \mbox{Max 39.5 mm (after 500 cycles)} \\ \mbox{Width (w)} & \mbox{Max 21.5 mm (after 500 cycles)} \end{array}$ 

Weight  $\sim 9.6 \text{ g}$ 

Charging Characteristic CC/CV – Constant Current / Constant Voltage

Voltage 4.35 V CV

Current Normal 0.5 C CC - 260 mAMax. Charging Current 1.0 C CC - 520 mATemperature at Charging  $0 \text{ °C} \dots 45 \text{ °C}$ 

## **Discharge Characteristic**

Cut off Voltage 3.0 V

Max discharge Current 2.0 C – 1040 mA ( for non continues discharge )

1.0 C – 520 mA ( for continues discharge )

Temperature during Discharge -20 °C ... 60 °C

Cycle Life at Room Temperature > 80% of minimum capacity after 500 cycles ( 0.5 C

charge, 0.5 C discharge)

Storage Temperature -20 °C ... 45 °C

( 0 °C ... 30 °C recommended in case of storage for

more than 3 months)

Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative. For safety related information please consult the ASDS document related to that product or product family. The Products of Renata SA are neither designed nor authorized for use in certain areas of application of environment. For further details we refer to our webpage <a href="https://www.renata.com/downloads/restriction\_of\_use">www.renata.com/downloads/restriction\_of\_use</a>

**Dimensions** 

Illustration only. For detailed drawing

please contact your sales

representative