


IFS204

IFB3004BBPKG/US-104





€	
---	--

LISTED		
Product characteristics		
Inductive sensor		
Metal thread M12 x 1		
Connector		
Increased sensing range		
Gold-plated contacts		
Sensing range 4 mm; [f] fl	ush mountal	ble
Electrical data		
Electrical design		DC PNP
Operating voltage	[V]	1030 DC
Current consumption	[mA]	< 10
Protection class		I
Reverse polarity protection	1	yes
Outputs		
Output function		normally open
Voltage drop	[V]	< 2.5
Current rating	[mA]	100
Short-circuit protection		yes
Overload protection		yes
Switching frequency	[Hz]	700
Range		
Sensing range	[mm]	4
Real sensing range (Sr)	[mm]	4 ± 10 %
Operating distance	[mm]	03.25
Accuracy / deviations		
Correction factors		mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.5 / Al approx. 0.4 / Cu
		approx. 0.3
Hysteresis	[% of Sr]	315
Switch-point drift	[% of Sr]	-1010
Environment	50.01	
Ambient temperature	[°C]	-2570
Protection		IP 67
Tests / approvals		
EMC		EN 61000-4-2 ESD: 4 kV CD / 8 kV AD EN 61000-4-3 HF radiated: 10 V/m
		EN 61000-4-4 Burst: 2 kV
		EN 61000-4-6 HF conducted: 10 V
		EN 55011: class B
MTTF	[Years]	1527



IFS204

IFB3004BBPKG/US-104



UL approval number		A003	
Mechanical data			
Mounting		flush mountable	
Housing materials		Brass white bronze coated; active face: PBT orange; LED window: PEI; lock nuts: Brass white bronze coated	
Weight	[kg]	0.024	
Displays / operating elements			
Output status indication	LED	4 x yellow	
Electrical connection			
Connection		M12 connector; Gold-plated contacts	
Wiring 3 4			
Accessories			
Accessories (included)		2 lock nuts	
Remarks			
Pack quantity	[piece]	1	

ifm electronic gmbh • Friedrichstraße 1 • 45128 Essen — We reserve the right to make technical alterations without prior notice. — GB — IFS204 — 06.10.2014