

Industrial-Grade Potentiometers

Series IP6000



Special features


- excellent linearity standard \pm 0.075%, on request \pm 0.025%
- long life 100 x 10⁶ movements typ.
- very good repeatability 0.007°
- mechanical continuous rotation
- protection class IP 65

This "industrial-grade" potentiometer has been specially designed for the severe working conditions often encountered in industrial applications. The housing is waterprotected and of sturdy construction. The shaft passage is sealed by a means of a gland, and the connector comes up to the degree of protection IP 65 with the conformable plug. Because of its reliability, long life, good linearity, high resolution, high operational speed and corrosion resistance, this component opens applications hitherto closed to conventional potentiometers.

If the operating wiper current is installed via connection 5, a protective resistance prevents a short circuit between the wiper and the supply voltage, as it can happen when wiring.

Special versions with different electrical travels and shaft dimensions are available.





Description		
Case	aluminium anodized, shaft passage sealed	
Shaft	stainless steel	
Bearings	stainles steel ball bearings	
Resistance element	conductive plastic	
Wiper assembly	precious metal multi-finger wiper	
Electrical connections	5-pin connector (see "Accessories").	

Novotechnik Messwertaufnehmer OHG

Postfach 4220 73745 Ostfildern (Ruit) Horbstraße 12 73760 Ostfildern (Ruit)

Tel. +49 711 44 89-0 Fax +49 711 44 89-150 info@novotechnik.de www.novotechnik.de

© 04/2010 Art.-Nr.: 062 710 Subject to changes Printed in Germany

Mechanical Data		
Dimensions	see drawing	
Mounting	with 3 clamps Z 3-31	
Mechanical travel	360, continuous	۰
Permitted shaft loading (axial and radial) static or dynamic force	45	N
Starting torque	<1.5	Ncm
Maximum operational speed	2 000	min ⁻¹
Weight	180	g
Electrical Data		
Actual electrical travel	355 ±2	۰
Nominal resistance	5	kΩ
Resistance tolerance	±20	%
Independent linearity	±0.075 (<0.05 on request)	%
Repeatability	0.002 (≙ 0.007°)	%
Effective temperature coefficient of the output-to-applied voltage ratio	typical 5	ppm/K
Max. permissible applied voltage	42	V
Max. wiper current in case of malfunction	10	mA
Protective resistance	5.6 kΩ between connection 2 and 5	
Recommended operating wiper current	≤1	μА
Insulation resistance (500 VDC)	≥ 10	MΩ
Dielectric strength (500 VAC, 50 Hz)	≤ 100	μА
Environmental Data		
Temperature range	-40+100	°C
Vibration	52000 A _{max} = 0.75 a _{max} = 20	Hz mm g
Shock	50 11	g ms
Life	100 x 10 ⁶	movem
Protection class	IP 65 (DIN 400 50 / IEC 529) (with plug EEM 33-70)	
Order designations		
Type	Art.no.	

010001

010004

 $90^{\circ} \pm 2^{\circ}$, indep. lin $\pm 0.3\%$

IP6501 A502

IP6501 G252

Additional models available

Included in delivery

3 mounting clamps Z3-31
Recommended accessories
Fork coupling Z 104 G 6
(backlash free),
Fork coupling Z 105 G 6
(backlash-free),
Mating plug EEM 33-70
protection class IP 67,
Right-angled plug EEM 33-72
protection class IP 40,
Process-controlled indicators
MAP... with display,
Signal conditioner MUP.../
MUK ... for standardized output signals

Important

All the values given in this data sheet for linearity, lifetime and temperature coefficient in the voltage dividing mode are quoted for the device operating with the wiper voltage driving on operational amplifier working as a voltage follower, where virtually no load is applied to the wiper ($l_e \le 1~\mu A$).

