



















## KEL-ER 16

# Cable Entry Frames



Also available with stainless steel screws (V2A).



Also available with threaded bushings.



Slit KT grommets

Steel serews (V2A).		Dustilligs.			
	Туре	Order No.	Grommets small   large	PU	Description
	KEL-ER 16 8  KEL-ER 16 8  with V2A screws	48168 48168.200	8 -	10	120 103 0 0 0 0 0
	KEL-ER 16 5  KEL-ER 16 5  with V2A screws	48165 48165.200	4 1 4 1	10	120 103 05,8
	KEL-ER 16 2  KEL-ER 16 2 with V2A screws	48162 48162.200	- 2 - 2	10	120 103 05,8



## **Product Description**

Split cable entry system for routing and sealing cables with connectors, providing an IP65 / up to NEMA type 4X rating and strain relief for cable diameters from 1 to 16 mm (KT 1 - 15) and 16 to 35 mm (KT 16 - 34).

The new cable entry system is easy to install. Cable grommets are placed into compartments in the frame and are securely fixed to the frame during assembly. The KEL-ER 16 frame matches exactly the cut-out dimensions for 16-pin standard industrial connectors. A flat rubber gasket is included in the shipment.

# Advantages & Benefits

- Warranty on pre-terminated cables remains
- Retrofits, repairs and maintenance can be done much more easily and quickly
- High cable density, wide variety of grommets
- Strain relief according to EN 62444
- High stability, vibration resistant

# Specifications

Material Polyamide (PA) Flame class UL94-Vo

IP65, with gasket and correct IP rating

selection of single grommets (certified acc. to EN 60529)

NEMA type rating NEMA type 4X (acc. to UL 50E) Temperature - 40°C to + 140°C (static)

- 40°F to + 284°F (static)

**Properties** Halogen-free, silicone-free **Cut-out dimensions** 36/46 × 86 mm / Page 200 - 201

Frame depth 17 mm

### Accessories

KT Cable grommets 44 - 46 KEL-EMC Grounding mounts 126 - 128 ST Plugs 49