













The ProLite TW1023ASC-B1P touch panel PC is a perfect choice for high-use environments such as retail, interactive POS, information desks or hospitality applications.

This 10.1" PCAP 10-point touchscreen with Android allows users to directly connect and operate the monitor from any device. The Power over Ethernet technology (POE) allows to provide both data connection and power by a single cable, simplifying all installations. This monitor can operate in landscape, portrait or face-up orientation. Together with the built-in camera and speakers it offers limitless interactive installation possibilities.



Android OS

Thanks to Android OS, you can easily customize the display to your needs by installing applications directly to it.



PoE (power-over-ethernet)

The Power over Ethernet technology (POE) allows to provide both data connection and power by a single cable, which simplifies installation in areas where many cables would interfere with the environment.

DISPLAY CHARACTERISTICS

| Design | Edge to edge glass |
|-------------------------|---|
| Diagonal | 10.1", 25.5cm |
| Panel | IPS Panel Technology, LED |
| Native resolution | 1280 x 800 |
| Aspect ratio | 16:10 |
| Brightness | 450 cd/m² typical |
| Brightness | 385 cd/m² with touch |
| Static contrast | 1000:1 with touch |
| Light transmittance | 85% |
| Response time (GTG) | 25ms |
| Viewing zone | horizontal/vertical: 160°/160°, right/left: 80°/80°, up/down: 80°/80° |
| Colour support | 16.7mln 8bit |
| Viewable area W x H | 216.6 x 135.4mm, 8.5 x 5.3" |
| Pixel pitch | 0.1692mm |
| Bezel colour and finish | black, matte |



| Touch technology | projective capacitive |
|-----------------------------|---|
| Touch points | 10 |
| Touch method | finger, glove (latex), capacitive stylus |
| Touch interface | USB |
| Supported operating systems | All iiyama monitors are Plug & Play and compatible with Windows and Linux. For details regarding the supported OS for the touch models, please refer to the driver instruction file available in the downloads section. |



03 INTERFACES / CONNECTORS / CONTROLS

| Digital signal output | HDMI x1 (mini HDMI, 1280x720 @60Hz) |
|-----------------------|-------------------------------------|
| Audio output | Speakers 2 x 1.5W |
| USB ports | x2 (2.0, 1 x MICRO with OTG) |
| RJ45 (LAN) | x1 |



FEATURES

| Integrated software | Android 8.1 without GMS |
|------------------------------|---|
| CPU | Rockchip RK3288, quad-core Cortex–A17 up to 1.8GHz |
| GPU | Mail-T760 MP4 |
| Storage | 16GB eMMC |
| Memory | 2GB DDR3 |
| Extra | Power-over-Ethernet, Android OS, webcam (2 megapixel), microphone & speakers, bluetooth 4.0, SD card slot, anti-fingerprint coating |
| Max. non-stop operating time | 24/7 |
| Glass thickness | 1.25mm |
| Glass hardness | 7H |



GENERAL

install new application / manage application, lock application, calculator, calendar, camera, chrome, alarm / clock / timer / stopwatch, email, manage files and folders, manage images / video / audio, organize albums, manage power on/off time, play audio files, search engine, system preferences, sound recorder, play video files

06 MECHANICAL

Orientation landscape, portrait, face-up

VESA mounting 75 x 75mm

07 ACCESSORIES INCLUDED

Guides quick start guide, safety guide

Other AC adapter

Cable cover yes

08 POWER MANAGEMENT

Power supply unit external

Power supply DC 12 V

Power usage 7W typical

09 SUSTAINABILITY

Regulations CE

Other REACH SVHC above 0.1%: Lead

10 DIMENSIONS / WEIGHT


 Product dimensions W x H x D
 255 x 172 x 30.5mm

 Box dimensions W x H x D
 398 x 223 x 68mm

 Weight (without box)
 0.8kg

 Weight (with box)
 1.36kg

 EAN code
 4948570117116



All trademarks and registered trademarks acknowledged. E & O E. Specification subject to change without notice. All LCD's comply with ISO-9241-307:2008 in connection with pixel defects.

© IIYAMA CORPORATION. ALL RIGHTS RESERVED