Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

 Postal address:
 36035 Fulda, Germany

 Phone:
 +49 661 6003-0

 Fax:
 +49 661 6003-607

 Email:
 mail@jumo.net

 Internet:
 www.jumo.net

JUMO UK LTD

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6724 Joy Road East Syracuse, NY 13057, USA

Phone: +1 315 437 5866
Fax: +1 315 437 5860
Email: info.us@jumo.net
Internet: www.jumousa.com



Data Sheet 401001

Page 1/8

JUMO MIDAS

OEM-Pressure Transmitter

Applications

- · Compressors
- · Mechanical and plant engineering
- Industrial Pneumatics
- Commercial vehicles
- · Building technology

Special features

- From 0 to 1,6 bar up to 0 to 100 bar, relative pressure
- Elastomer-sealed
- · Compact design: from 58 mm length
- · High chemical resistance
- · High mechanical strength membrane

Description

The pressure transmitter is used for pressure measurement of liquid and gaseous media. With the well proofed ceramic thick film sensor, the pressure is measured, converted into an electrical standard signal (voltage or current) and output via electrical connections, e.g. line socket, M12 plug connector or attached cable.

A large number of process connections are available for adaptation to the process.



Type 401001

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO UK LTD JUMO House

Temple Bank, Riverway
Harlow, Essex, CM20 2DY, UK
Phone: +44 1279 63 55 33
Fax: +44 1279 62 50 29
Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6724 Joy Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860

Email: info.us@jumo.net

Internet: www.jumousa.com

JUMO

Data Sheet 401001

Page 2/8

Technical data

Electrical safety

Requirements	DIN EN 61010-1: 2020
	The device must be equipped with an electrical circuit that meets the requirements for "Limited-
	energy circuits".

Electrical data

Output signal ^a	4 to 20 mA, two-wire	DC 0.5 to 4.5 V, three-wire, ratiometric ^b	DC 0 to 10 V, three-wire
Burden or load ^c	$R_B \le (U_B - 10 \text{ V}) \div 0.02 \text{ A}$	R _L ≥ 20 kΩ	R _L ≥ 10 kΩ
Output current	3.6 to 22 mA	-20 to +250 μA	-20 μA to +1 mA
Voltage supply U _B ^d	DC 10 to 30 V	DC 4.75 to 5.25 V	DC 11.5 to 30 V
Nominal voltage	DC 24 V	DC 5 V	DC 24 V
Voltage supply influence	≤ 0.02 %/V	≤ 0.02 %/V	≤ 0.02 %/V
Current consumption ^e	≤ 25 mA	≤ 5 mA	≤ 5 mA
Reverse voltage protection	Yes	No	Yes
Short-circuit resistance ^f	-	No	Yes
Step response T ₉₀	≤ 3 ms	≤ 3 ms	≤ 3 ms

Output signal ^a	DC 1 to 5 V, three-wire	DC 1 to 6 V, three-wire	DC 0 to 10 V, three-wire, increased driver power
Burden or load ^c	R _L ≥ 10 kΩ	R _L ≥ 10 kΩ	$R_L \ge 2 k\Omega$
Output current	-20 μA to +1 mA	-20 μA to +1 mA	-200 μA to +5 mA
Voltage supply U _B ^d	DC 8 to 30 V	DC 8 to 30 V	DC 11.5 to 30 V
Nominal voltage	DC 24 V	DC 24 V	DC 24 V
Voltage supply influence	≤ 0.02 %/V	≤ 0.02 %/V	≤ 0.02 %/V
Current consumption ^e	≤ 5 mA	≤ 5 mA	≤ 5 mA
Reverse voltage protection	Yes	Yes	Yes
Short-circuit resistance ^f	Yes	Yes	Yes
Step response T ₉₀	≤ 3 ms	≤ 3 ms	≤ 3 ms

^a Further outputs are available upon request.

b Ratiometric output: output signal from 10 to 90 % of the voltage supply

c Load resistance to S-

^d Residual ripple: The voltage peaks or dips must not exceed or fall below the specified voltage supply values!

^e For no-load operation (output unloaded)

f Short-circuit resistance S+ against V-

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO UK LTD

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6724 Joy Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866

Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 401001

Page 3/8

Inputs

Measuring range and accuracy

Measuring range	asuring range Linearity ^a Accuracy at				Overload ^c	Burst
		20 °C ^d	-20 to +100 °Ce	stability ^b		
bar	% MSP ^f	% MSP	% MSP	% MSP per year	bar	bar
0 to 1.6 bar relative pressure	0.3	0.5	1.6	≤ 0.2	6	12
0 to 2.5 bar relative pressure	0.3	0.5	1.6		6	12
0 to 4 bar relative pressure	0.3	0.5	1.6		12	25
0 to 6 bar relative pressure	0.25	0.5	1.4		12	25
0 to 10 bar relative pressure	0.25	0.5	1.4		20	38
0 to 16 bar relative pressure	0.25	0.5	1.4		50	75
0 to 25 bar relative pressure	0.25	0.5	1.4		50	75
0 to 40 bar relative pressure	0.25	0.5	1.4		120	200
0 to 60 bar relative pressure	0.25	0.5	1.4		120	200
0 to 100 bar relative pressure	0.25	0.5	1.4		180	250
-1 to +0.6 bar relative pressure	0.3	0.6	1.6		6	12
-1 to +1.5 bar relative pressure	0.3	0.6	1.6		6	12
-1 to +3 bar relative pressure	0.3	0.6	1.6		12	25
-1 to +5 bar relative pressure	0.25	0.6	1.4		12	25
-1 to +9 bar relative pressure	0.25	0.6	1.4		20	38
-1 to +15 bar relative pressure	0.25	0.6	1.4		50	75
-1 to +24 bar relative pressure	0.25	0.6	1.4		50	75

a Linearity according to limit point-setting, DIN EN 61298-2

b Reference conditions DIN EN 61298-1

^c All pressure transmitter are vaccum proof.

^d Includes: linearity, hysteresis, repeatability, deviation from measuring range start (offset), and measuring range end

e Includes: linearity, hysteresis, repeatability, deviation from measuring range start (offset) and measuring range end, thermal influences on measuring range start (offset), and measuring span

f MSP = measuring span

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany Phone: +49 661 6003-0 Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO UK LTD JUMO House

Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6724 Joy Road East Syracuse, NY 13057, USA

Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 401001

Environmental influences

Admissible temperatures	
Medium	-20 to +125 °C
Ambient	-20 to +85 °C
Storage	-40 to +125 °C (for version with connecting cable -20 to +100 °C)
Admissible air humidity	
Operation	100 % relative humidity including condensation on the device outer case
Storage	90 % elative humidity without condensation
Admissible mechanical load	IEC 60068-2-6, IEC 60068-2-27
Vibration resistance	20 g for 10 to 2000 Hz
Shock resistance	100 g for 1 ms
Electromagnetic compatibility (EMC)	DIN EN 61326-1:2013, DIN EN 61326-2-3:2013
Interference emission	Class B ^a
Interference immunity	Industrial requirements
Protection type	DIN EN 60529
Connecting cable	IP67
M12 plug connector ^b	IP67
Line socket ^{b, c}	IP65

The product is suitable for industrial use as well as for households and small businesses.

Mechanical features

Stainless steel 305
FPM, standard
CR
FFPM
FPM
Ceramic Al ₂ O ₃ 96 %,
Measuring principle: Thick film on ceramic body (piezoresistive)
Stainless steel 305
PBT-GF30, PVC
PBT-GF30, stainless steel 303 L
PBT-GF30, PA, silicone
> 10 million, 0 to 100 % measuring range
Any
Device upright, process connection at the bottom
100 g with process connection G 1/4"

Note the medium durability of the selected seal material!

The protection type is only achieved with a suitable mounted counter piece.

Connecting cable diameter, minimum 5mm, maximum 8 mm

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO UK LTD

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29

Email: sales@jumo.co.uk Internet: www.jumo.co.uk JUMO Process Control, Inc.

6724 Joy Road East Syracuse, NY 13057, USA

Phone: +1 315 437 5866
Fax: +1 315 437 5860
Email: info.us@jumo.net
Internet: www.jumousa.com





Data Sheet 401001


Page 5/8

Dimensions


Device











Process connections














V5.00/EN/00398114/2023-10-10

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

Postal address: 36035 Fulda, Germany
Phone: +49 661 6003-0
Fax: +49 661 6003-607
Email: mail@jumo.net
Internet: www.jumo.net

JUMO UK LTD

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk

Internet: www.jumo.co.uk

JUMO Process Control, Inc. 6724 Joy Road

East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net

Internet: www.jumousa.com



Data Sheet 401001

Page 6/8

Connection elements

The connection elements in the data sheet provide information on product selection.

For the electrical connection, only use the installation instructions or the operating manual.

Terminal assignment



Designation	Description	Assignment ^a					
to 20 mA, two-wire U _B /S+ WH (white) /oltage supply DC 10 to 30 V BN (brown)		1 WH (white) 3 BN (brown)	1 WH (white) 2 BN (brown)				
DC 0.5 to 4.5 V, Dreileiter, ratiometric Voltage supply DC 4.75 to 5.25 V	U _B 0 V/S- S+	WH (white) BN (brown) YE (yellow)	1 WH (white) 2 BN (brown) 3 YE (yellow)	1 WH (white) 2 BN (brown) 3 YE (yellow)			
DC 0 to 10 V, three-wire Voltage supply DC 11.5 to 30 V	U _B 0 V/S- S+	WH (white) BN (brown) YE (yellow)	1 WH (white) 2 BN (brown) 3 YE (yellow)	1 WH (white) 2 BN (brown) 3 YE (yellow)			
DC 1 to 5(6) V, three-wire Voltage supply DC 8 to 30 V	U _B 0 V/S- S+	WH (white) BN (brown) YE (yellow)	1 WH (white) 2 BN (brown) 3 YE (yellow)	1 WH (white) 2 BN (brown) 3 YE (yellow)			
Functional bonding conductor FB ^b	<i></i>	-	4	\(\begin{array}{c} \\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ 			

The color coding is only valid for A-coded standard cables!

b The pressure transmitter has to be connected to the potential equalization system of the plant via the electrical connection or process connection

Delivery address: Mackenrodtstraße 14

36039 Fulda, Germany 36035 Fulda, Germany +49 661 6003-0 Postal address: Phone: Fax: +49 661 6003-607 Email: mail@jumo.net Internet: www.jumo.net

JUMO UK LTD JUMO House

Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29 Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6724 Joy Road East Syracuse, NY 13057, USA

Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 401001

Order details

	(1)	Basic type
401001/000	(1)	JUMO MIDAS – OEM-Pressure transmitter
401001/000	(2)	Input
455	(2)	0 to 1,6 bar relative pressure
456		0 to 2.5 bar relative pressure
457		0 to 4 bar relative pressure
458		0 to 6 bar relative pressure
459		0 to 10 bar relative pressure
460		0 to 16 bar relative pressure
461		0 to 25 bar relative pressure
462		0 to 40 bar relative pressure
463		
		0 to 60 bar relative pressure
464 479		0 to 100 bar relative pressure ^a
		-1 to +0.6 bar relative pressure
480		-1 to +1,5 bar relative pressure
481		-1 to +3 bar relative pressure
482		-1 to +5 bar relative pressure
483		-1 to +9 bar relative pressure
484		-1 to +15 bar relative pressure
485		-1 to +24 bar relative pressure
999		Special measuring range relative pressure
	(3)	Output
405		4 to 20 mA, two-wire
412		0.5 to 4.5 V, three-wire
415		0 to 10 V, three-wire
418		1 to 5 V, three-wire
420		1 to 6 V, three-wire
	(4)	Process connection
501		G 1/8" according to DIN EN 837
502		G 1/4" according to DIN EN 837
511		1/4-18 NPT according to DIN EN 837
521		G 1/4" according to DIN 3852-11
523		G 1/2" according to DIN 3852-11
562		7/16-20 UNF external
	(5)	Process connection material
20		CrNi (stainless steel)
	(6)	Seal
601		FPM (standard)
602		CR
604		FFPM
	(7)	Electrical connection
11		Connecting cable (standard cable length is 2 m, further lengths available upon request)
36		M12 plug connector
61		Line socket DIN EN 175301-803, form A

Delivery address: Mackenrodtstraße 14 36039 Fulda, Germany

36035 Fulda, Germany +49 661 6003-0 Postal address: Phone: Fax: +49 661 6003-607 Email: mail@jumo.net www.jumo.net Internet:

JUMO UK LTD

JUMO House Temple Bank, Riverway Harlow, Essex, CM20 2DY, UK Phone: +44 1279 63 55 33 Fax: +44 1279 62 50 29

Email: sales@jumo.co.uk Internet: www.jumo.co.uk

JUMO Process Control, Inc.

6724 Joy Road East Syracuse, NY 13057, USA Phone: +1 315 437 5866 Fax: +1 315 437 5860 Email: info.us@jumo.net Internet: www.jumousa.com



Data Sheet 401001

	(8)	Extra code
000		None
591		Choke in the pressure channel
624		Oil and grease free
630		Enlarged pressure channel
954		Technical Passport

Only available in conjunction with extra code 630.

	(1)		(2)		(3)		(4)		(5)		(6)		(7)		(8)		
Order code		-		-		-		-		-		-		/		, ²	3
Order example	401001/000	-	460	-	412	-	502	-	20	-	601	-	36	/	591		

List extra codes in sequence, separated by commas.

Accessories

Designation	Part no.
Line socket, 4-pole, M12 × 1, straight, length 2 m	00404585
Line socket, 4-pole, M12 × 1, angled, length 2 m	00409334
Line socket, 4-pole, M12 × 1, with control cable, 5 m	00512341