

SMD Tweezers

- » Smooth handling and positioning of all SMD components
- » Different tips and angles for specific applications
- » Satin antiglare finish and ergonomic design
- » Good corrosion resistance to most chemicals & acids
- » Available as reverse action model




SM100.SA
4 1/2" 115 mm
Reverse action tweezers for handling SMDs for PCBs





SM101.SA
4 1/2" 115 mm
Reverse action tweezers for soldering and de-soldering 8, 14 or 16 Lead SMDs



SM102.SA
4 1/2" 115 mm
Reverse action tweezers for soldering and de-soldering 20, 28, 44 and 68 LCCC and PLCC pad devices





SM103.SA
4 1/2" 115 mm
For handling and positioning 2 and 3 lead SOT packages at 45° angle



SM104.SA

4 3/4" 120 mm


For handling and positioning 3 lead SOT packages, monolithic chip capacitors, etc.



SM105.SA

4 3/4" 120 mm


Special design for positioning all SOT packages vertically



SM106.SA

4 3/4" 120 mm




For positioning all SOT packages horizontally; flat base tips (4 mm long)



SM107.SA

4 3/4" 120 mm


For positioning all flat devices at 60° angle



SM108.SA

4 3/4" 120 mm


For positioning and soldering 1mm wide components



SM109.SA

4 1/4" 120 mm


Same as SM108 but with 45° tips without anti-crush feature



SM110.SA

4 3/4" 120 mm


For positioning monolithic chips capacitors, grooved tips



SM111.SA

4 3/4" 120 mm


For positioning 5 mm monolithic chip capacitors; flat base grooved tips (2 mm long)



SM112.SA

4 3/4" 120 mm




For positioning 5 mm monolithic chip capacitors at 60°, grooved tips



SM113.SA

4 3/4" 120 mm


3 mm long tips bent at 60° angle one forked blade lead entry



SM114.SA

4 3/4" 120 mm

Same as SM113 but with straight tips for vertical holding



SM115.SA

4 3/4" 120 mm


Grooved tips at 30° angle for holding and positioning cylindrical devices (up to 0.5 mm diam.)



SM116.SA

4 3/4" 120 mm

Grooved straight tips, for vertical positioning of cylindrical devices (up to 0.5 mm diam. or more)



SM117.SA

4 3/4" 120 mm

For positioning SOT packages at 30° angle



K5SMDF

SMD precision tweezers set

SM103, SM107, SM108, SM111, SM115 in top quality hard/foam wallet