
efector150°

KG5066

KG-3120NFPKGP2T/US **Capacitive sensors**





1: LED ring 2: Programming buttons





Made in Germany

C C CUL)US		wade in Cermany
Product characteristics		
Capacitive sensor		
Plastic thread M18 x 1		
Connector		
Sensing range 12 mm; [nf]	non-flush r	mountable
Application		
Application		For dry bulk material and liquids. Optimised for media with a dielectric constant < 20 (e.g. oils, plastic granulates).
Electrical data		
Electrical design		DC PNP
Operating voltage	[V]	1036 DC

Electrical design		DC PNP
Operating voltage	[V]	1036 DC
Current consumption	[mA]	< 20
Protection class		II
Reverse polarity protection		yes

Outputs		
Output function		normally open / closed programmable
Voltage drop	[V]	< 2.5
Current rating	[mA]	200
Short-circuit protection		pulsed
Overload protection		yes
Switching frequency	[Hz]	10
Pange		

Range		
Sensing range	[mm]	12
Real sensing range (Sr)	[mm]	12 ± 10 %
Accuracy / deviations		

	water = 1 / glass approx. 0.4 / ceramics approx. 0.2 / PVC approx. 0.1	
[% of Sr]	115	
[% of Sr]	-2020	

Elivirolillielit		
Ambient temperature	[°C]	-2580, temperature of the sensing face -25110 °C
Target medium temperature	[°C]	110
Protection		IP 65 / IP 67

Tests / approvals			
EMC		IEC 60947-5-2:	1997 + A1: 1999 + A2: 2003
MTTF	[Years]		662

efector15°

KG5066

Accessories

Remarks

Accessories (included)

KG-3120NFPKGP2T/US



Mechanical data				
Mounting		non-flush mountable		
Housing materials		housing: PBT; connector: PC; buttons: TPE-U		
Weight	[kg]	0.063		
Displays / operating elem	Displays / operating elements			
Output status indication	LED	yellow (LED ring and connector light translucently)		
Electrical connection				
Connection		M12 connector		
Wiring				
301		1		
ŭ 1	\Diamond	<u>3</u> □ L-		

Pack quantity [piece] 1

ifm electronic gmbh • Friedrichstraße 1 • 45128 Essen — We reserve the right to make technical alterations without prior notice. — GB — KG5066 — 09.11.2010

2 lock nuts