

Kilovac EV600 High Voltage Contactor

Rugged 600 Amp Contactor Featuring Bi-Directional Power Switching and Increased Rupture Capability

Kilovac EV600 High Voltage Contactor

Rugged 600 Amp Contactor Featuring Bi-Directional Power Switching and Increased Rupture Capability



RUGGED

• Designed for harsh environments

VERSATILE BI-DIRECTIONAL POWER SWITCHING

- Not polarity sensitive
- Withstands higher current pulse without levitation

RELIABLE

- Rated at 600 Amps
- Increased current interrupting capability
- Increased rupture and dielectric capability

ENHANCED PERFORMANCE

- Dual coil electronic "cut-throat" economization increases low power holding capability
- Eliminates the possibility of noise caused by PWM

Description

The EV600 high voltage contactor is designed for harsh environments offering higher continuous current carrying rating, and improved current interrupting capability over our existing EV200.

Key enhanced features include:

- Bi-directional power switching with increased rupture capability and dielectric life
- Dual coil economization that improves low power holding capability
- · Form A auxiliary contact

APPLICATIONS

- Power Distribution
- Motor Control Circuit Isolation
- Circuit Protection
- Alternative Energy
- Energy and Battery Storage

MARKETS

- Military Ground Vehicles
- Commercial Ground Vehicles
- Test Equipment
- Charging Systems

TE Components . . . TE Technology . . . TE Know-how . . . AMP | AGASTAT | CII | HARTMAN | KILOVAC | MICRODOT | NANONICS | POLAMCO | Raychem SEACON | Rochester | DEUTSCH

Empower Engineers to Solve Problems, Moving the World Forward.



Performance Characteristics

Electrical

Voltage Rating: Main Contacts (1)	Vdc	28-1000		
Current Rating, Continuous: Main Contacts (2)	Α	600A		
Contact Resistance: Main Contacts (3)	mΩ	0.2 max @ 600A		
	mV	110 max @ 600A		
Aux Contacts:	mΩ	150 @ 1A		
Hot Switching Performance, Resistive Load				
200A make/ break @ +/-400Vdc	cycles	4000		
600A make/break @ +/-400Vdc	cycles	10		
3000A carry/break @ +/400Vdc	cycles	2		
Maximum pulse through closed contacts (4)	Amps	+/-4000		
Mechanical Life (min)	cycles	100,000		
Dielectric Withstand Voltage				
Terminal to Terminal	•	10kVdc		
Terminals to Coil		3950Vdc		
Insulation resistance				
Terminal to Terminal/Terminals to Coil		100M Ω min @ 500Vdc		
		$50 \text{M}\Omega$ min @ 500Vdc end of life		


- (1) Maximum Load Interrupt at 1000Vdc = 250Adc
- (2) Keep relay terminals below 150°C max continuous, 175°C max for two hours, and 200°C for 1 minute.
 214 mm sq. conductor size recommended for 600A carry (2X 4/0 AWG). See derating curve for current vs. ambient temperature operating ambient to +85°C allowed with current derating.
- (3) Stabilized reading.
 Contact resistance may
 exceed spec in the first 3
 minutes of current carry.
- (4) 1ms rise time, 10ms pulse duration.
- (5) Minimum Load: 5V/5mA
- (6) Ambient conditions and conductor size affect rating.

Mechanical

Contact Arrangements: Main Contacts		SPST Form X
Auxiliary Contacts (3A/125Vrms or 1A/30Vdc) (5)		SPST Form A
Dimensions	In [mm]	See dimensions, below
Weight, Nominal	Kg	0.56

Environmental

Shock, 11ms 1/2 sine (operating)	Gpeak	20
Sine Vibration, 20 G _{peak}	Hz	55-2000
Operating/Storage Temperature Range (6)	°C	-55 to +85
Operating Altitude (max)	ft	70,000



TE Part No.	Description
4-1618413-9	EV600 High Voltage Contactor, 24 Volt Coil
5-1618413-0	EV600 High Voltage Contactor, 12 Volt Coil




Coil Data

Coil Data @ 20C (Internal Two-Coil Economizer)

		12V Coil	24/28V Coil
Coil Voltage Range	Vdc	9-14	18-28
Nominal Pickup Current	А	5.5	4.5
Nominal Holding Current	А	0.25	0.30
Pickup Voltage	Vdc	≥ 9	≥ 16
Dropout Voltage	Vdc	≤ 3.5	≤ 10
Pickup Pulse (max)	ms	75	75
Coil Resistance +/-5%	Ω	2.0 Pickup/43 Hold	5.7 Pickup/104 Hold
Coil Holding Power	W	3.2	5.3
Main Contacts:		20	20
Operate Time (max)	ms		
Operate Bounce (max)	ms	3	3
Release Time	ms	5	5

Schematic



EV600 (Electronic Cut-Throat Economizer)


Coil Wire: 22 AWG, Red = +, Black = Return Auxiliary: 22 AWG; White = NO White = COM

All wires Raychem FLHTC6009-22, 1kV rated




Continuous Current vs. Ambient Temperature - EV600

2x 4/0 AWG [214 mm^2] conductor Max Terminal Temperature <170C Contacts Closing into > 10Adc



Continuous Current vs. Temperature



Estimated Load Switching Life vs. Voltage and Current (Break-Only >650A)

LET'S CONNECT

We make it easy to connect with our experts and are ready to provide all the support you need. Just call your local support number or visit te.com to chat with a Product Information Specialist.

Technical Support

te.com/support-center

North America +1 800 522 6752

North America (Toll) +1 717 986 7777

EMEA/South Africa +800 0440 5100

EMEA (Toll) +31 73 624 6999

India (Toll-Free) +800 440 5100

Asia Pacific +86 400 820 6015

Japan +81 044 844 8180

Australia +61 2 9554 2695

New Zealand +64 (0) 9 634 4580

te.com/kilovac-ev600

AMP, AGASTAT, CII, DEUTSCH, HARTMAN, KILOVAC, MICRODOT, NANONICS, POLAMCO, Raychem, SEACON, TE, TE Connectivity and the TE connectivity (logo) are trademarks owned or licensed by TE Connectivity. Other products, logos, and company names mentioned herein may be trademarks of their respective owners.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information herein, nothing herein constitutes any guarantee that such information is error-free, or any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. The TE entity issuing this publication reserves the right to make any adjustments to the information contained herein at any time without notice. All implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose are expressly disclaimed. The dimensions herein are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice.

Consult TE for the latest dimensions and design specifications

© 2019 TE Connectivity All Rights Reserved.

2357833-1 07/19

