

Contact-Type Digital Tachometer

KPS-TC10



- Measurement of rotation speeds of motors and linear speeds of conveyor belts
- Linear speed unit selection: m / min, m / sec, ft / min, ft / sec, inch / min
- Hold readings on screen
- Retention of maximum and minimum values - Record of up to 100 measurements
- Auto power off and low battery indicator
- Backlit display
- Supply with the different couplings to carry out the specified measurements
- Tested and certified according to IEC / EN 61326

KPS-TC10

Contact-Type Digital Tachometer

General	
Product Size	170mm×60mm×27mm
Product Weight	130g
Power Supply	4×1.5V AAA Batteries
Certificate	CE/ETL/RoHS

Specs	
Measuring Mode	Contact
Idler wheel selection (6", 12", 0.1m)	✓
Unit Selection (m/min, m/sec, ft/min, ft/sec, in/min)	✓
Auto Power Off	✓
MAX/MIN	✓
Data Logging (100 groups)	✓
Data Hold	✓
Display Backlight	✓
Low Battery Display	✓

KPS-TC10

Contact-Type Digital Tachometer

UNITS	SCALE	RESOLUTION	ACCURACY
Angular Velocity	50 ~ 99.99 rpm	0.01 rpm	± (0.03% + 2 digits)
	100 ~ 9999.9 rpm	0.1 rpm	± (0.03% + 2 digits)
	10000 ~ 19999 rpm	1 rpm	± (0.03% + 2 digits)

Product Code Information

SKU	KPSTC10CBINT
EAN code	8435394710402
UPC code	810053670569
Pcs/export carton	20