### Keysight Technologies

# 6610C Series Single-Output, 40–50 W GPIB Power Supplies

### Speed and accuracy for test optimization

- Small, compact size for bench and system use
- Fast, low-noise outputs
- Dual-range, precision low current measurement
- Built-in measurements and advanced programmable features
- Protection features to ensure DUT safety

Data Sheet





This series of linear-regulated 40-50 W DC power supplies is designed to maximize the throughput of DUTs through the manufacturing test process with fast programming and measurement, and also active downprogramming. It offers many advanced programmable features including stored states and status reporting. Programming is done using industry standard SCPI commands via the GPIB or RS-232. Test system integration is further simplified by using the VXI*plug&play* drivers. The optional relays simplify system design and troubleshooting.

The half-rack size of the 6610C series makes it a convenient DC power supply for the R&D lab bench. The built-in microamp measurement system helps the engineer to easily and accurately monitor the output voltage and current without a complicated test setup.

### Specifications

<b>Specifications</b> (at 0 ° to 55 ° unless otherwise spec	cified)	6611C	6612C	6613C	6614C	6611C-J05 Special Order Option
Number of outputs		1	1	1	1	1
GPIB		Yes	Yes	Yes	Yes	Yes
Output ratings Voltage Current		0 to 8 V 0 to 5 A	0 to 20 V 0 to 2 A	0 to 50 V 0 to 1 A	0 to 100 V 0 to 0.5 A	0 to 10 V 0 to 5 A
Programming accuracy at 25 °C Voltage Current	C ± 5 °C 0.05% +	5 mV 2 mA	10 mV 1 mA	20 mV 0.75 mA	50 mV 0.5 mA	5 mV 2 mA
Ripple and noise 20 Hz to 20 MHz;with outputs u or with either terminal grounded Voltage Normal mode		0.5 mV 3 mV 2 mA	0.5 mV 3 mV 1 mA	0.5 mV 4 mV 1 mA	0.5 mV 5 mV 1 mA	0.5 mV 3 mV 2 mA
DC measurement accuracy via GPIB or front-panel meters to actual output at 25 °C ± 5 °C Voltage Low current range -20 mA to + 20 mA High current range +20 mA to + rated I -20 mA to - rated I		2 mV 2.5 μA 0.5 mA 1.1 mA	3 mV 2.5 μA 0.25 mA 0.85 mA	6 mV 2.5 μA 0.2 mA 0.8 mA	12 mV 2.5 μA 0.1 mA 0.7 mA	2 mV 2.5 μA 0.5 mA 1.1 mA
Load regulation Voltage Current		2 mV 1 mA	2 mV 0.5 mA	4 mV 0.5 mA	5 mV 0.5 mA	2 mV 1 mA
Line regulation Voltage Current		0.5 mV 0.5 mA	0.5 mV 0.5 mA	1 mV 0.25 mA	1 mV 0.25 mA	0.5 mV 0.5 mA

Transient response time

Less than 100  $\mu$ s for the output to recover to its previous level (within 0.1% of the voltage rating of the supply or 20 mV, whichever is greater) following any step change in load current of up to 50% of the output current rating of the supply

Supplemental Characteristics (Non-warranted characteristics determined by design and useful in applying the product)	6611C	6612C	6613C	6614C	<b>6611C-J05</b> Special order option
Average programming resolution Voltage Current	2 mV 1.25 mA	5 mV 0.5 mA	12.5 mV 0.25 mA	25 mV 0.125 mA	3 mV 1.25 mA
Sink current	3 A	1.2 A	0.6 A	0.3 A	3 A

## Supplemental characteristics for all model numbers

DC floating voltage: Output terminals can be floated up to  $\pm$  240 VDC maximum from chassis ground

Remote sensing: Up to two volts dropped in each load lead. Add 2 mV to the voltage load regulation specification for each one volt change in the positive output lead due to load current change.

Command processing time: Average time required for the output voltage to begin to change following receipt of digital date is 4 ms for the power supplies connected directly to the GPIB.

Output programming response time: The rise and fall time (10/90% and 90/10%) of the output voltage is less than 2 ms. The output voltage change settles within 1 LSB (0.025% x rated voltage) of final value in less than 6 ms.

GPIB interface capabilities: IEEE-488.2, SCPI command set, and 6610A/B Series programming compatibility

Input power: (full load): 1.6 A, 100 W (6611C: 2.2 A, 120 W)


Regulatory compliance: Complies with EMC directive 89/336/EEC (ISM 1B).

Software driver: VXIplug&play

Size: 212.8 mm W x 88.1 mm H x 368.3 mm D (8.4 in x 3.5 in x 14.5  $\cdot$  ).

Weight: 8.2 kg (18.16 lb) net; 10.6 kg (23.5 lb) shipping

Keysight Models: 6611C, 6612C, 6613C, 6614C, 6611C-J05



#### Ordering information

Opt 100	87 to 106 VAC, 47 to 63 Hz
Opt 120	104 to 127 VAC, 47 to 63 Hz
Opt 220	191 to 233 VAC, 47 to 63 Hz
Opt 230	207 to 253 VAC, 47 to 63 Hz
Opt 760	Isolation and reversal relays

Opt 0L1 Full documentation on CD-ROM, and printed

Removes feet for use in rack system

standard documentation package. CD-ROM includes User's Guide, Programming Guide, Service Manual and Quick Start Guide

Opt 0B3 Printed service manual

Accessories

Opt 87J

p/n 1494-0015 Rack slide kit

E3663AC\* Support rails for Keysight rack cabinets

1CM002A\* Rack mount flange kit 88.1 mm H (2U), 1.5 inch

hole space for side by side mounting of two units.

Requires lock link kit (and support rails)

5061-9694 Lock link kit

1CM024A\* Rack mount flange kit 88.1 mm H (2U), one

bracket, one half-module bracket, and filler panel

#### Application notes

10 Practical Tips You Need to Know About Your Power Products, 5965-8239E 10 Hints for Using Your Power Supply to Decrease Test Time, 5968-6359E Understanding Linear Power Supply Operation (AN1554), 5989-2291EN

\*Support rails required

#### www.keysight.com/find/6610

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: www.keysight.com/find/contactus

This information is subject to change without notice. © Keysight Technologies, 2012 - 2017 Published in USA, December 5, 2017 5990-9301EN

www.keysight.com

