

KPTF-1616RGBC-11

1.6 x 1.6 mm Full-Color Surface Mount LED



DESCRIPTIONS

- The Hyper Red source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode
- · The Green source color devices are made with InGaN on Sapphire Light Emitting Diode
- The Blue source color devices are made with InGaN Light Emitting Diode
- · Electrostatic discharge and power surge could damage the LEDs
- . It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- · All devices, equipments and machineries must be electrically grounded

FEATURES

- 1.6 mm x 1.6 mm SMD LED, 0.7 mm thickness
- · Low power consumption
- Can produce any color in visible spectrum, including white light
- Package: 2000 pcs / reel
- Moisture sensitivity level: 3
- RoHS compliant

APPLICATIONS


- Backlight
- · Status indicator
- · Home and smart appliances
- · Wearable and portable devices
- · Healthcare applications

ATTENTION

Observe precautions for handling electrostatic discharge sensitive devices




PACKAGE DIMENSIONS



RECOMMENDED SOLDERING PATTERN

(units: mm; tolerance: ± 0.1)



- Tolerance is ±0.2(0.008") unless otherwis
- 3. The specifications, characteristics and technical data described in the datasheet are subject to
- change without prior notice.

 4. The device has a single mounting surface. The device must be mounted according to the specifications.

SELECTION GUIDE

Part Number	Emitting Color (Material)	Lens Type	Iv (mcd) @ 20mA [2]		Viewing Angle [1]	
			Min.	Тур.	201/2	
KPTF-1616RGBC-11	Hyper Red (AlGaInP)	Water Clear	55	110		
	Green (InGaN)		120	280	130°	
	■ Blue (InGaN)		40	70		

Notes.

1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.

2. Luminous intensity / luminous flux: +/-15%.

3. Luminous intensity value is traceable to CIE127-2007 standards.





ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

Dougnoston	Symbol	Emitting Color	Value		Unit
Parameter	Symbol	Emitting Color	Тур. Мах.		
Wavelength at Peak Emission I _F = 20mA	λ_{peak}	Hyper Red Green Blue	630 515 460	-	nm
Dominant Wavelength I _F = 20mA	λ _{dom} ^[1]	Hyper Red Green Blue	621 525 465	-	nm
Spectral Bandwidth at 50% Φ REL MAX I _F = 20mA	Δλ	Hyper Red Green Blue		-	nm
Capacitance	С	Hyper Red Green Blue	25 45 100	-	pF
Forward Voltage I _F = 20mA	V _F ^[2]	Hyper Red Green Blue	2 3.3 3.3	2.5 4.1 4	V
Reverse Current (V _R = 5V)	I _R	Hyper Red Green Blue	-	10 50 50	uA

Notes:

ABSOLUTE MAXIMUM RATINGS at T_A=25°C

Damandan	Symbol	Value			
Parameter		Hyper Red	Green	Blue	Unit
Power Dissipation	P_{D}	75	102.5	120	mW
Reverse Voltage	V _R	5	5	5	V
Junction Temperature	T _j	115	115	115	°C
Operating Temperature	T _{op}	-40 to +85			°C
Storage Temperature	T _{stg}	-40 to +85			°C
DC Forward Current	I _F	30	25	30	mA
Peak Forward Current	I _{FM} ^[1]	195	150	150	mA
Electrostatic Discharge Threshold (HBM)	-	3000	450	250	V

Notes:
1. 1/10 Duty Cycle, 0.1ms Pulse Width.
2. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.




^{1.} The dominant wavelength (\(\lambda\)) above is the setup value of the sorting machine. (Tolerance \(\lambda\ddot\): \(\pm \text{1nm.}\))
2. Forward voltage: \(\pm \text{2.1V.}\)
3. Wavelength value is traceable to CIE127-2007 standards.
4. Excess driving current and \(\rangle\) or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.




TECHNICAL DATA







SPATIAL DISTRIBUTION




HYPER RED


Forward Current vs. Forward Voltage T_a = 25 °C 40 Forward current (mA) 30 20 10 0 2.1 2.3 1.5 1.9 1.7 Forward voltage (V)










GREEN













BLUE












TECHNICAL DATA


REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS




- Don't cause stress to the LEDs while it is exposed to high temperature
 The maximum number of reflow soldering passes is 2 times.
- The maximum number of reflow soldering passes is 2 times.

 Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.

TAPE SPECIFICATIONS (units: mm)



REEL DIMENSION (units: mm)



PACKING & LABEL SPECIFICATIONS





PRECAUTIONARY NOTES

- The information included in this document reflects representative usage scenarios and is intended for technical reference only
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
- The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.

 The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
- All design applications should refer to Kingbright application notes available at http://

