

Keysight U1190 Series Clamp Meters

Data Sheet





Introduction

Keysight Technologies, Inc., U1190 Series clamp meters are packed with a wealth of features to help you work more conveniently and more safely. Designed in a robust case—the unique wire separator makes it easy to measure individual wires in a bundle. The built-in LED flashlight illuminates your test area while Vsense performs non-contact voltage detection. What’s more, the U1190 Series clamp meters are CAT III 600 V and CAT IV 300 V certified. Use Keysight U1190 Series clamp meters and retool your expectations in handheld tools.

Features

The U1190 Series clamp meters include:

- Unique wire separator to separate wires from a bundle
- Vsense to perform non-contact voltage detection¹
- Built-in LED flashlight to illuminate test area¹
- Visual (backlight alert) and audible continuity indication in noisy environments
- Current measurement up to 600 A²
- Digital multimeter (DMM) with resistance, capacitance¹, DCV, ACV, DCA³, ACA, DC μ A³ and AC μ A³ measurement capabilities
- Continuity and diode test measurements
- CAT III 600 V / CAT IV 300 V safety rating

1. Exclusive to U1192A, U1193A, and U1194A.
2. Exclusive to U1193A and U1194A.
3. Exclusive to U1194A.

Unique wire separator with a built-in flashlight

The U1190 Series clamp meters are built to perform in the environments you work. The unique wire separator allows you to effortlessly isolate and perform measurements on individual wires in a bundle. For improved visibility when making measurements, these clamp meters also come with an easily activated built-in LED flashlight that illuminates the test area. These features ensure that you are better equipped when making measurements.



Figure 1. The unique wire separator allows you to separate and measure individual wires more easily

Vsense for non-contact voltage detection

The U1190 Series clamp meters have Vsense—a unique method of non-contact voltage detection that safeguards users from exposure to hot or live wires while making measurements in dangerous working environments. Upon the detection of voltage, a unique safety alert of an audible beeper is produced to alert users.

Ergonomically built with current measurement up to 600 A

Ergonomically built, the U1190 Series clamp meters fit comfortably in the palm of your hand and allow you to select measurement functions with just a simple thumb press. Better yet, the U1193A and U1194A come with a current measurement up to 600 A. The wide range of current measurement functions cover an array of applications such as electrical installation, maintenance, and troubleshooting tasks—making it an ideal tool to use across many industrial applications.

Take a Closer Look



1. Exclusive to U1192A, U1193A, and U1194A.

2. Exclusive to U1194A.



Figure 2. Built-in LED flashlight to illuminate test area

Model Comparison

	U1191A	U1192A	U1193A	U1194A
Basic features				
Display	6,000 counts	6,000 counts	6,000 counts	6,000 counts
RMS method	Average responding	Average responding	True RMS	True RMS
Measurement range				
DC voltage	600 V	60 to 600 V	60 to 600 V	60 to 600 V
AC voltage	600 V	60 to 600 V	60 to 600 V	60 to 600 V
DC current	–	–	–	60 to 600 A
DC μ A current	–	–	–	60 to 600 μ A
AC current	400 A	60 to 400 A	60 to 600 A	60 to 600 A
AC μ A current	–	–	–	60 to 600 μ A
Resistance	600 Ω to 6 k Ω	600 Ω to 60 k Ω	600 Ω to 60 k Ω	600 Ω to 60 k Ω
Capacitance	–	600 μ F to 6 mF	600 μ F to 6 mF	600 μ F to 6 mF
Diode	1.5 V	1.5 V	1.5 V	1.5 V
Continuity	600 Ω	600 Ω	600 Ω	600 Ω
Temperature	–	–	–	K-type: -40 to 1,200 °C
Frequency	–	99.99 Hz to 99.99 kHz	99.99 Hz to 99.99 kHz	99.99 Hz to 99.99 kHz
Data management				
Data hold	Yes	Yes	Yes	Yes
Null	Yes	Yes	Yes	Yes
MAX/MIN/AVG	Yes	Yes	Yes	Yes
Auto/Range	Yes ¹	Yes	Yes	Yes
Other features				
Built-in LED flashlight	No	Yes	Yes	Yes
Auto power OFF	Yes	Yes	Yes	Yes
Clamp opening	31 mm	31 mm	37 mm	37 mm
Clamping diameter	27 mm	27 mm	35 mm	35 mm
Safety and regulatory				
Over-voltage safety protection	CAT III 600 V/ CAT IV 300 V	CAT III 600 V/ CAT IV 300 V	CAT III 600 V/ CAT IV 300 V	CAT III 600 V/ CAT IV 300 V
EN/IEC 61010-1, CE, CSA compliance	Yes	Yes	Yes	Yes

1. Applicable to Resistance range only.

Electrical Specifications

Specification assumptions:

Accuracy is given as \pm (% of reading + counts of least significant digit) at $23\text{ }^{\circ}\text{C} \pm 5\text{ }^{\circ}\text{C}$, with relative humidity less than 80% RH. AC voltage and AC current specifications for U1193A and U1194A are AC coupled, true rms and are valid from 5% of range to 100% of range. The crest factor may be up to 3.0 at 4,000 counts. For non-sinusoidal waveforms, add additional accuracy of (2% reading + 2% full scale) typically. In the EMC RF field of 3 V/m, total accuracy is specified as specified accuracy + 30 digits for all functions.

DC specifications

Function	Range	Resolution	Accuracy			
			U1191A	U1192A	U1193A	U1194A
Voltage						
	60 V	0.01 V	–	0.5% + 3	0.5% + 3	0.5% + 3
	600 V	0.1 V	0.5% + 3	0.5% + 3	0.5% + 3	0.5% + 3
Resistance						
	600 Ω	0.1 Ω	0.8% + 5	0.8% + 5	0.8% + 5	0.8% + 5
	6 k Ω	0.001 k Ω	0.8% + 3	0.8% + 3	0.8% + 3	0.8% + 3
	60 k Ω	0.01 k Ω	–	0.8% + 3	0.8% + 3	0.8% + 3
Diode						
	1.5 V	0.001 V	1.0% + 3	1.0% + 3	1.0% + 3	1.0% + 3
Current						
	60 μA	0.01 μA	–	–	–	1.0% + 5
	600 μA	0.1 μA	–	–	–	1.0% + 5
	60 A	0.01 A	–	–	–	2.0% + 5
	600 A	0.1 A	–	–	–	2.0% + 5

Notes for DC voltage specification:

1. Input impedance of 10 M Ω .

Notes for resistance specifications:

1. Overload protection: 600 Vrms for short circuits with < 0.1 mA current.
2. Maximum open voltage is < 1.4 V.
3. The accuracy is specified after the Relative function is used to subtract the test lead resistance and thermal effect (by shorting the test leads).

Notes for diode specifications:

1. Overload protection: 600 Vrms for short circuits with < 0.4 mA current.
2. Maximum open voltage is 1.8 V.
3. Built-in buzzer beeps continuously when the voltage measured is less than 100 mV and beeps once for forward-biased diode or semiconductor junctions measured between 0.3 and 0.8 V ($0.3\text{ V} \leq \text{reading} \leq 0.8\text{ V}$).

Notes for DC current specifications:

1. DC current measurement is only available for U1194A model.
2. 60 to 600 A ranges are from clamp current measurement. 60 to 600 μA ranges are from digital multimeter measurement.
3. Overload protection for 60 to 600 A range: 600 Arms.
4. Position error: 1% from reading.
5. Use Relative mode to zero residual offset.

Electrical Specifications

AC voltage specification

Range	Resolution	Voltage accuracy (45 to 500 Hz)	
		U1191A	U1192/3/4A
60 V	0.01 V	–	1.2% + 5
600 V	0.1 V	1.2% + 5	1.2% + 5

Notes for AC voltage:

1. Input impedance 10 M Ω (nominal) in parallel with < 100 pF.
2. Frequency response: 45 to 500 Hz (sine wave).

AC current specification

Range	Resolution	U1191A ³		U1192A ³		U1193A ⁴		U1194A ⁴	
		Current accuracy (45 to 65 Hz)	Current accuracy (65 to 500 Hz)	Current accuracy (45 to 65 Hz)	Current accuracy (65 to 500 Hz)	Current accuracy (45 to 65 Hz)	Current accuracy (65 to 500 Hz)	Current accuracy (45 to 65 Hz)	Current accuracy (65 to 500 Hz)
60 μ A	0.01 μ A	–	–	–	–	–	–	1.0% + 5	1.0% + 5
600 μ A	0.1 μ A	–	–	–	–	–	–	1.0% + 5	1.0% + 5
60 A	0.01 A	–	–	2.0% + 5	3.0% + 5	2.0% + 5	3.0% + 5	2.0% + 5	3.0% + 5
400 A	0.1 A	2.0% + 5	3.0% + 5	2.0% + 5	3.0% + 5	–	–	–	–
600 A	0.1 A	–	–	–	–	2.0% + 5	3.0% + 5	2.0% + 5	3.0% + 5

Notes for AC current:

1. Frequency response: 45 to 500 Hz (sine wave).
2. Position error: 1% of reading.
3. AC conversion type for U1191A and U1192A: Average sensing, RMS indication.
4. AC conversion type for U1193A and U1194A: RMS sensing, RMS indication.
5. Maximum overload: 400 A RMS.
6. For non-sinusoidal waveform, add additional accuracy of (2% reading + 2% full scale) typically for crest factor ≥ 3.0 .

Capacitance specifications

Range	Resolution	Accuracy	
		U1191A	U1192/3/4A
600 μ F	0.1 μ F	–	2.0% + 4
6 mF	0.001 mF	–	2.0% + 4

Notes for capacitance specifications:

1. Capacitance measurement is not available with U1191A model.
2. Overload protection: 600 Vrms for short circuits with < 0.1 mA current.
3. The accuracy for all ranges is specified based on a film capacitor or better, and use Relative mode.

Electrical Specifications

Temperature specifications

Thermal type	Range	Resolution	Accuracy
			U1194A
K	-40 to 400 °C	0.1 °C	1.0% + 2.0 °C
	400 to 1,200 °C	1.0 °C	1.0% + 2.0 °C
	-40 to 752 °F	0.1 °F	1.0% + 3.6 °F
	752 to 2,192 °F	1.0 °F	1.0% + 3.6 °F

Notes for temperature specifications:

1. Temperature measurement is only available with the U1194A model.
2. The accuracy does not include the tolerance of the thermocouple probe, and the meter should be put on a place that has been operating for a minimum of one hour.
3. Do not allow the temperature sensor to contact a surface that is energized above 30 Vrms or 60 V DC. Such voltage poses a shock hazard.
4. The temperature calculation is specified according to the safety standards of EN/IEC-60548-1 and NIST175.
5. Accuracy specification assumes the surrounding temperature is stable with ± 1 °C. For the surrounding temperature changes of ± 3 °C, rated accuracy applies after two hours.

Frequency specifications

Range	Resolution	Accuracy
		U1192/3/4A
99.99 Hz	0.01 Hz	0.5% + 3
999.9 Hz	0.1 Hz	0.5% + 3
9.999 kHz	0.001 kHz	0.5% + 3
99.99 kHz	0.01 kHz	0.5% + 3

Notes for frequency specifications:

1. Exclusive to U1192A, U1193A, and U1194A.
2. Overload protection: 600 V.
3. Minimum frequency is 10 Hz.

Frequency Sensitivity Specifications

For voltage measurements

Input range	Minimum sensitivity (rms sine wave)	
	10 Hz to 10 kHz	10 to 60 kHz
Maximum input for specified accuracy	U1192/3/4A	
60 V	6.0 V	30 V
600 V	60 V	-

For current measurements

Input range	Minimum sensitivity (rms sine wave)
	45 Hz to 1 kHz
Maximum input for specified accuracy	U1192/3/4A
60 A	6.0 A
600 A	60 A

Continuity specifications

Range	Resolution	Accuracy				Test current
		U1191A	U1192A	U1193A	U1194A	
600 Ω	0.1 Ω	0.8% + 5	0.8% + 5	0.8% + 5	0.8% + 3	0.1 mA

Notes for continuity specifications:

1. Overload protection: 600 Vrms for short circuits with < 0.1 mA current.
2. Maximum open voltage is 1.4 V.
3. Built-in buzzer beeps continuously when the reading measured is less than 30 Ω and does not beep when the measured resistance is more than 200 Ω . Buzzer may either sound or not between 30 Ω and 200 Ω .
4. Continuity indicator: 2.7 kHz tone buzzer.

Measuring rate (approximate)

Function	Times/second			
	U1191A	U1192A	U1193A	U1194A
AC V	3	3	3	3
DC V	3	3	3	3
Ω	2	2	2	2
Diode	3	3	3	3
Capacitance	-	2 times/second for 600 μ F 1 time/9 seconds for 6 mF	2 times/second for 600 μ F 1 time/9 seconds for 6 mF	2 times/second for 600 μ F 1 time/9 seconds for 6 mF
Temperature	-	-	-	2
DC A	-	-	-	3
AC A	3	3	3	3
Frequency	-	3 (> 10 Hz)	3 (> 10 Hz)	3 (> 10 Hz)

Product Characteristics

Power supply	
Battery type	2 x 1.5 V AAA Alkaline battery
Battery life	<ul style="list-style-type: none"> - Approximately 40 hours with backlight on - Approximately 200 hours with backlight off and continuous DC voltage measurement
Power consumption	<ul style="list-style-type: none"> - Approximately 9 mVA with backlight off and DC voltage measurement - Approximately 42 mVA with backlight on and DC voltage measurement
Display	Liquid crystal display (LCD) (with maximum reading of 6,000 counts)
Operating environment	<ul style="list-style-type: none"> - Operating temperature from -10 to 50°C, 0 to 80% RH - Altitude up to 2,000 meters - Pollution degree II
Relative humidity (RH)	Relative humidity up to 80% RH for temperature up to 30 °C decreasing linearly to 50% RH at 50 °C
Storage compliance	-40 to 60 °C, 40% to 80% RH without batteries
Safety compliance	<ul style="list-style-type: none"> - Low Voltage Directive (2006/95/EC) - IEC 61010-1:2001/EN 61010-1:2001 - IEC 61010-2-032:2002/EN 61010-2-032:2002 - CAN/CSA-C22.2 No. 61010-1-04 - CAN/CSA-C22.2 No. 61010-2-032-04 - ANSI/UL Std No. 61010-1:2004
Measurement category	CAT III 600 V / CAT IV 300 V
Electromagnetic compatibility (EMC)	<ul style="list-style-type: none"> - EMC Directive (2004/108/EC) - IEC 61326-1:2005/EN61326-1:2006 - Canada: ICES/NMB-001: Issue 4, June 2006 - Australia/New Zealand: AS/NZS CISPR 11:2004
Temperature coefficient	0.1 x (specified accuracy)/°C (from 0 to 18 °C, or 28 to 50 °C)
Common mode rejection ratio (CMRR)	<ul style="list-style-type: none"> > 60 dB at 50/60 Hz in the AC V function > 120 dB at DC, 50/60 Hz in the DC V function
Dimensions (W x H x D)	U1191/2A: 77.1 x 225.0 x 38.6 mm U1193/4A: 77.1 x 238.0 x 38.6 mm
Weight (with batteries)	U1191/2A: 320 g U1193A: 334 g U1194A: 348 g
Calibration cycle	One year

Ordering Information



Standard shipped items

Certificate of calibration

Quick Start Guide

K-type thermocouple (only for U1194A)

1.5 V AAA Alkaline battery

Soft carrying case

Test leads with 4-mm tips

Recommended accessories

U1168A Standard test lead kit

U1169A Test Probe Leads

U1176A LED Probe Clip Light

U1178A Soft carrying case

U1181A Immersion temperature probe

U1182A Industrial surface temperature probe

U1183A Air temperature probe

U1184A Temperature probe adaptor

U1186A K-type thermocouple extension grade

U1188A K-type thermocouple grade

Evolving Since 1939

Our unique combination of hardware, software, services, and people can help you reach your next breakthrough. We are unlocking the future of technology.

From Hewlett-Packard to Agilent to Keysight.



For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at:

www.keysight.com/find/contactus

Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:

www.keysight.com/find/contactus
(BP-9-7-17)

DEKRA Certified
ISO 9001 Quality Management System

www.keysight.com/go/quality
Keysight Technologies, Inc.
DEKRA Certified ISO 9001:2015
Quality Management System

myKeysight

myKeysight

www.keysight.com/find/mykeysight

A personalized view into the information most relevant to you.

http://www.keysight.com/find/emt_product_registration

Register your products to get up-to-date product information and find warranty information.

KEYSIGHT SERVICES

Accelerate Technology Adoption.
Lower costs.

Keysight Services

www.keysight.com/find/service

Keysight Services can help from acquisition to renewal across your instrument's lifecycle. Our comprehensive service offerings—one-stop calibration, repair, asset management, technology refresh, consulting, training and more—helps you improve product quality and lower costs.

Keysight Assurance Plans

www.keysight.com/find/AssurancePlans

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

Keysight Channel Partners

www.keysight.com/find/channelpartners

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.



www.keysight.com/find/U1190clamp



This information is subject to change without notice.
© Keysight Technologies, 2017
Published in USA, December 1, 2017
5990-8646EN
www.keysight.com