



HIGH FREQUENCY PROBE

Z3431-2 High Frequency Probe



Z3431-2 High Frequency Probe:
100 kHz - 750 MHz, 0.25 ... 50 VAC.

In combination with a multimeter, the Z3431-2 high frequency probe allows for measurement of alternating voltages with amplitudes of 0.25 to 50 V within a frequency range of 100 kHz to 750 MHz.

The probe rectifies alternating voltages at a ratio of 1:1. The measuring instrument must have an input impedance of 10 MΩ.

Type	Article
Z3431-2	GTZ3431002R0001

CABLE SETS

Cable Sets with Permanently Mounted Test Probes



KS17-ONE KS17-2 KS29



KS17-S




(adjustable test probe, CATII / CAT IV)
KS-AP



KS-NTS



KS21-T



KY95-3

Z502U



KY94

Cable sets with permanently mounted test probes and contact-protected angle plugs for safe measuring

Hook clips, alligator clips or push-on lugs can be attached to the test probes for special measuring tasks.

- KS17-ONE cable set:
600 V / CAT III, 1 A, 120 cm long
600 V / CAT II, 16 A
- KS29 cable set:
1000 V / CAT III, 1 A safety cable set for power meters
- KS17-2 cable set:
S1000 V / CAT III, 1 A, 600 V / CAT IV, 1 A
1000 V / CAT II, 16 A, 120 cm long
- KS17-S cable set:
1000 V / CAT II, 150 cm long,
stainless steel test probes, 2 mm diameter
- KS-AP cable set:
1000 V / CAT II, 19 A, 1000 V / CAT IV, 1 A, with
adjustable test probes, 115 cm long
4 mm angle plug
- KS-NTS cable set:
1000 V / CAT II / III, 20 A,
double insulated silicon measurement cables,
120 cm long, with one pair each of small test
probes, alligator clips, clip hooks and North
American test probes
- KS21-T cable set
1000 V / CAT II, 16 A,
200 cm long for cable multimeter
- KY95-3 alligator clip:
1000 V / CAT III, 16 A,
- Magnetic test probes with 4 mm plug
1000 V / CAT III, 4 A
- KY94 hook clips (1 pair)

Type	Article
KS17-ONE	Z110K
KS29	Z229A
KS17-2	GTY3620034P0002
KS17-S	Z110H
KS-AP	Z110S
KS-NTS	Z110W
KS21-T	Z110U
KY95-3	Z110J
Magnetic test probes - 4 mm	Z502U
KY94	GTY3610094P01