Product data sheet Characteristics

LADT2

Time delay contact block,TeSys Deca,1NO +1NC,on-delay 1-30s,front





Main

Iviaiii	
Range	TeSys TeSys Deca
Product name	TeSys Deca
Product or component type	Time delay auxiliary contact block
Range compatibility	TeSys D CAD TeSys D LC1D TeSys F LC1F TeSys F CR1F TeSys Deca CAD TeSys Deca LC1D
Mounting location	Front
Pole contact composition	1 NO + 1 NC
Auxiliary contacts operation	Time delay
Timer type	On delay
Time delay range	130 s
[Ue] rated operational voltage	690 V AC 25400 Hz
[le] rated operational current	6 A at 120 V AC-15 1.04 A at 690 V AC-15 0.55 A at 125 V DC-13 0.1 A at 600 V DC-13
[Ui] rated insulation voltage	690 V conforming to IEC 60947-5-1 600 V conforming to UL 60947-5-1 600 V conforming to CSA C22.2 No 60947-5-1
[Ith] conventional free air thermal current	10 A (at 60 °C)
Standards	CSA C22.2 No 60947-5-1 GB/T 14048.5 EN/IEC 60947-5-1
Product certifications	IECEE CB Scheme UL CSA CCC EAC UKCA

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products by specific user applications. It is the douty of any sub-user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or substituies shall be responsible or liable for misuse of the information contained herein.

Complementary

Complementary	
Irms rated making capacity	140 A at <= 690 V AC conforming to IEC 60947-5-1
	250 A at <= 690 V DC conforming to IEC 60947-5-1
Permissible short-time rating	100 A 60 °C 1 s
	120 A 60 °C 500 ms
	140 A 60 °C 100 ms
Protection type	GG fuse 10 A
Mechanical durability	5 Mcycles
Minimum switching current	5 MA
Minimum switching voltage	17 V
Non-overlap time	1.5 Ms on de-energisation no overlap between NC and NO contact
	1.5 Ms on energisation no overlap between NC and NO contact
Insulation resistance	> 10 MOhm
Connections - terminals	Screw clamp terminals 1 cable(s) 12.5 mm²flexible with cable end
	Screw clamp terminals 1 cable(s) 12.5 mm²flexible without cable end
	Screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end
	Screw clamp terminals 2 cable(s) 12.5 mm²flexible without cable end
	Screw clamp terminals 1 cable(s) 12.5 mm²rigid
	Screw clamp terminals 2 cable(s) 12.5 mm²rigid
	Screw clamp terminals
Tightening torque	1.7 N.M - with screwdriver flat Ø 6 mm
	1.7 N.M - with screwdriver Philips No 2
	1.7 N.M - with screwdriver pozidriv No 2
Height	48 Mm
Width	44 Mm
Depth	61 Mm
Colour	Dark grey

Environment

Normal environment
IP20 conforming to IEC 60529
TH conforming to IEC 60068
-6080 °C
-4070 °C
3000 m

Packing Units

r doming office	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.2 Cm
Package 1 Width	6.5 Cm
Package 1 Length	5 Cm
Package 1 Weight	74 G
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	5.2 Cm
Package 2 Width	13 Cm
Package 2 Length	24 Cm
Package 2 Weight	752 G
Unit Type of Package 3	S03
Number of Units in Package 3	140
Package 3 Height	30 Cm
Package 3 Width	30 Cm
Package 3 Length	40 Cm
Package 3 Weight	11 Kg



Offer Sustainability

REACh Declaration
V
Yes
Compliant EEU RoHS Declaration
Yes
China RoHS Declaration
€Yes
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Yes

Product Life Status : Commercialised