



Main

Range of product	TeSys D
Product or component type	Contacteur
Device short name	LC1D
Contacteur application	Motor control Resistive load
Utilisation category	AC-1 AC-3
Control circuit type	AC
Coil type	Standard
Poles description	3P
Pole contact composition	3 NO
Control circuit voltage	230 V AC 50/60 Hz

Complementary

Coil technology	Without built-in bidirectional peak limiting diode suppressor
Protective cover	With
[Ie] rated operational current	25 A ≤ 60 °C AC AC-3 power circuit 40 A ≤ 60 °C AC AC-1 power circuit
Motor power kW	5,5 kW 220...240 V AC 50/60 Hz 11 kW 380...400 V AC 50/60 Hz 11 kW 415 V AC 50/60 Hz 11 kW 440 V AC 50/60 Hz 15 kW 500 V AC 50/60 Hz 15 kW 660...690 V AC 50/60 Hz
Motor power hp	2 hp 115 V 1P AC 60 Hz UL 2 hp 115 V 1P AC 60 Hz CSA 3 hp 230/240 V 1P AC 60 Hz UL 3 hp 230/240 V 1P AC 60 Hz CSA 7,5 hp 230/240 V 3P AC 60 Hz CSA 7,5 hp 230/240 V 3P AC 60 Hz UL 7,5 hp 200/208 V 3P AC 60 Hz CSA 7,5 hp 200/208 V 3P AC 60 Hz UL 15 hp 460/480 V 3P AC 60 Hz CSA 15 hp 460/480 V 3P AC 60 Hz UL 20 hp 575/600 V 3P AC 60 Hz CSA 20 hp 575/600 V 3P AC 60 Hz UL
Auxiliary contacts type	Mechanically linked IEC 60947-5-1 1 NO + 1 NC Mirror contact IEC 60947-4-1 1 NC
Auxiliary contact composition	1 NO + 1 NC
Control circuit voltage limits	0.3...0.6 Uc 60 °C drop-out 50/60 Hz 0.8...1.1 Uc 60 °C operational 50 Hz 0.85...1.1 Uc 60 °C operational 60 Hz
[Ui] rated insulation voltage	600 V UL power circuit 600 V CSA power circuit 600 V UL control circuit 600 V CSA control circuit 690 V IEC 60947-1 power circuit 690 V IEC 60947-1 control circuit
[Uimp] rated impulse withstand voltage	6 kV IEC 60947
Overvoltage category	III
Mounting support	Plate Rail
Flame retardance	V1 UL 94

Das vorliegende Dokument beinhaltet allgemeine Beschreibungen und/oder technische Eigenschaften der Leistungsfähigkeit der hierin enthaltenen Produkte. Anhand des vorliegenden Dokuments soll nicht die Eignung und Zuverlässigkeit dieser Produkte für bestimmte Benutzeranwendungen festgelegt werden. Es stellt auch keinen Ersatz dafür dar. Es obliegt dem Benutzer oder Integrator, eine vollständige Risikoabschätzung sowie eine Bewertung und Prüfung der Produkte hinsichtlich ihres entsprechenden Einsatzes durchzuführen. Schneider Electric Industries SAS und die entsprechenden Tochter- oder Konzerngesellschaften übernehmen nicht die Haftung für den missbräuchlichen Gebrauch der hier enthaltenen Informationen.

Connections - terminals	Screw clamp terminal control circuit 2 1...4 mm ² solid without Screw clamp terminal control circuit 1 1...4 mm ² solid without Screw clamp terminal control circuit 2 1...2,5 mm ² flexible with Screw clamp terminal control circuit 1 1...4 mm ² flexible with Screw clamp terminal control circuit 2 1...4 mm ² flexible without Screw clamp terminal control circuit 1 1...4 mm ² flexible without Screw clamp terminal power circuit 2 1,5...6 mm ² solid without Screw clamp terminal power circuit 1 1,5...6 mm ² solid without Screw clamp terminal power circuit 2 1...4 mm ² flexible with Screw clamp terminal power circuit 1 1...6 mm ² flexible with Screw clamp terminal power circuit 2 1,5...6 mm ² flexible without Screw clamp terminal power circuit 1 1,5...10 mm ² flexible without
Tightening torque	1,7 N.m control circuit screw clamp terminal flat Ø 6 mm 1,7 N.m control circuit screw clamp terminal Philips No 2 2 mm 2,5 N.m power circuit screw clamp terminal flat Ø 6 mm 2,5 N.m power circuit screw clamp terminal Philips No 2 2 mm
[Ue] rated operational voltage	<= 690 V AC 25...400 Hz power circuit
[Ith] conventional free air thermal current	10 A ≤ 60 °C control circuit 40 A ≤ 60 °C power circuit
Irms rated making capacity	140 A AC control circuit IEC 60947-5-1 450 A 440 V power circuit IEC 60947
Rated breaking capacity	450 A 440 V power circuit IEC 60947
Associated fuse rating	10 A gG control circuit IEC 60947-5-1 40 A gG <= 690 V type 2 power circuit 63 A gG <= 690 V type 1 power circuit
Average impedance	2 mOhm 50 Hz 40 A power circuit
Power dissipation per pole	1,25 W AC-3 3,2 W AC-1
Inrush power in VA	70 VA 20 °C 0,75 50 Hz 70 VA 20 °C 0,75 60 Hz
Hold-in power consumption in VA	7 VA 20 °C 0,3 50 Hz 7,5 VA 20 °C 0,3 60 Hz
Operating time	4...19 ms opening 12...22 ms closing
Safety reliability level	B10d 1369863 cycles contactor with nominal load EN/ISO 13849-1 B10d 20000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical durability	15000000 cycles
Operating rate	3600 cyc/h ≤ 60 °C
Minimum switching current	5 mA control circuit
Minimum switching voltage	17 V control circuit
Non-overlap time	1,5 ms on de-energisation between NC and NO contacts 1,5 ms on energisation between NC and NO contacts
Insulation resistance	> 10 MOhm control circuit
Height	85 mm
Width	45 mm
Depth	92 mm
Product weight	0,37 kg

Environment

Standards	CSA C22-2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
Product certifications	BV CCC CSA DNV (Det Norske Veritas) GL GOST LROS (Lloyds register of shipping) RINA UL
IP degree of protection	IP2x VDE 0106 IP2x IEC 60529
Protective treatment	TH IEC 60068 3
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-60...80 °C
Permissible ambient air temperature around the device	-40...70 °C at U _c
Operating altitude	3000 m without
Fire resistance	850 °C IEC 60695-2-1
Shock resistance	8 gn contactor opened 15 gn contactor closed
Vibration resistance	2 gn contactor opened 5...300 Hz 4 gn contactor closed 5...300 Hz
Heat dissipation	2...3 W 50/60 Hz control circuit
RoHS EUR conformity date	0627
RoHS EUR status	Compliant