


# LC1K0601U7TQ

contactor TeSys LC1-K - 3 poles - AC-3 - 440 V 6 A  
- coil 230/240 V AC



## Main

Range of product	TeSys K
Range	TeSys
Product or component type	Contacteur
Device short name	LC1K
Contacteur application	Motor control
Utilisation category	AC-3 AC-4
Control circuit type	AC
Coil type	AC 50/60 Hz
Poles description	3P
Pole contact composition	3 NO
[Ie] rated operational current	6 A (<= 60 °C) at <= 440 V AC AC-3 for power circuit
Motor power kW	1.5 kW at 220...230 V AC 50/60 Hz AC-3 2.2 kW at 380...415 V AC 50/60 Hz AC-3 3 kW at 660/690 V AC 50/60 Hz AC-3 1.5 kW at 400 V AC 50/60 Hz AC-4 3 kW at 440/500 V AC 50/60 Hz AC-3
Motor power hp	1.5 hp at 200/208 V AC 60 Hz conforming to CSA 1.5 hp at 200/208 V AC 60 Hz conforming to UL 1.5 hp at 230/240 V AC 60 Hz conforming to CSA 1.5 hp at 230/240 V AC 60 Hz conforming to UL 3 hp at 460/480 V AC 60 Hz conforming to CSA 3 hp at 460/480 V AC 60 Hz conforming to UL 3 hp at 575/600 V AC 60 Hz conforming to CSA 3 hp at 575/600 V AC 60 Hz conforming to UL
Auxiliary contact composition	1 NC
[Uc] control circuit voltage	230/240 V AC 50/60 Hz
Connections - terminals	Power circuit : screw clamp terminal 1 cable 1.5 mm <sup>2</sup> - cable stiffness: solid Power circuit : screw clamp terminal 2 cable 4 mm <sup>2</sup> - cable stiffness: solid Power circuit : screw clamp terminal 1 cable 0.75 mm <sup>2</sup> - cable stiffness: flexible Power circuit : screw clamp terminal 2 cable 4 mm <sup>2</sup> - cable stiffness: flexible Power circuit : screw clamp terminal 1 cable 0.34 mm <sup>2</sup> - cable stiffness: flexible Power circuit : screw clamp terminal 1 cable 1.5 mm <sup>2</sup> - cable stiffness: flexible Power circuit : screw clamp terminal 1 cable 2.5 mm <sup>2</sup> - cable stiffness: flexible Control circuit : screw clamp terminal 1 cable 1.5 mm <sup>2</sup> - cable stiffness: solid Control circuit : screw clamp terminal 2 cable 4 mm <sup>2</sup> - cable stiffness: solid Control circuit : screw clamp terminal 1 cable 0.75 mm <sup>2</sup> - cable stiffness: flexible Control circuit : screw clamp terminal 2 cable 4 mm <sup>2</sup> - cable stiffness: flexible Control circuit : screw clamp terminal 1 cable 0.34 mm <sup>2</sup> - cable stiffness: flexible Control circuit : screw clamp terminal 1 cable 1.5 mm <sup>2</sup> - cable stiffness: flexible Control circuit : screw clamp terminal 1 cable 2.5 mm <sup>2</sup> - cable stiffness: flexible Power circuit : spring terminal 1 cable 0.75 mm <sup>2</sup> - cable stiffness: solid Power circuit : spring terminal 1 cable 1.5 mm <sup>2</sup> -

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

cable stiffness: solid  
 Power circuit : spring terminal 1 cable 0.75 mm<sup>2</sup> -  
 cable stiffness: flexible  
 Power circuit : spring terminal 1 cable 1.5 mm<sup>2</sup> -  
 cable stiffness: flexible  
 Control circuit : spring terminal 1 cable 0.75 mm<sup>2</sup> -  
 cable stiffness: solid  
 Control circuit : spring terminal 1 cable 1.5 mm<sup>2</sup> -  
 cable stiffness: solid  
 Control circuit : spring terminal 1 cable 0.75 mm<sup>2</sup> -  
 cable stiffness: flexible  
 Control circuit : spring terminal 1 cable 1.5 mm<sup>2</sup> -  
 cable stiffness: flexible  
 Power circuit : Faston connectors 2 - width: 2.8  
 mm - cable stiffness: clip  
 Power circuit : Faston connectors 1 - width: 6.35  
 mm - cable stiffness: clip  
 Control circuit : Faston connectors 2 - width: 2.8  
 mm - cable stiffness: clip  
 Control circuit : Faston connectors 1 - width: 6.35  
 mm - cable stiffness: clip

## Complementary

Coil technology	Without built-in bidirectional peak limiting diode suppressor
Control circuit voltage limits	$\geq 0.20 U_c$ at $\leq 50$ °C drop-out 50/60 Hz $0.8...1.15 U_c$ at $\leq 50$ °C operational 50/60 Hz
[Ui] rated insulation voltage	690 V for control circuit conforming to BS 5424 690 V for control circuit conforming to IEC 60947 690 V for power circuit conforming to BS 5424 690 V for power circuit conforming to IEC 60947 690 V for power circuit conforming to NF C 20-040 750 V for control circuit conforming to VDE 0110 group C 750 V for power circuit conforming to VDE 0110 group C 600 V for control circuit conforming to CSA C22.2 No 14 600 V for power circuit certifications UL 508 conforming to CSA C22.2 No 14
[Uimp] rated impulse withstand voltage	8 kV
Mounting support	Plate Rail
Flame retardance	Class C2 conforming to NF F 16-101 Class C2 conforming to NF F 16-102 V1 conforming to UL 94
Tightening torque	Power circuit : 0.8...1.3 N.m - on screw clamp terminal - with screwdriver flat $\varnothing$ 6 mm Power circuit : 0.8...1.3 N.m - on screw clamp terminal - with screwdriver Philips No 2
[Ue] rated operational voltage	$\leq 690$ V AC $\leq 400$ Hz for power circuit
[Ith] conventional free air thermal current	10 A at $\leq 50$ °C for control circuit 20 A at $\leq 50$ °C for power circuit
Irms rated making capacity	110 A at 690 V AC for control circuit conforming to IEC 60947 110 A at 690 V AC for power circuit conforming to IEC 60947 110 A at 690 V AC for power circuit conforming to NF C 63-110
Rated breaking capacity	110 A at 220...230 V for power circuit conforming to IEC 60947 110 A at 220...230 V for power circuit conforming to NF C 63-110 110 A at 380...400 V for power circuit conforming to IEC 60947 110 A at 380...400 V for power circuit conforming to NF C 63-110 110 A at 415 V for power circuit conforming to IEC 60947 110 A at 415 V for power circuit conforming to NF C 63-110 110 A at 440 V for power circuit conforming to IEC 60947 110 A at 440 V for power circuit conforming to NF C 63-110 70 A at 660...690 V for power circuit conforming to IEC 60947 70 A at 660...690 V for power circuit conforming to NF C 63-110 80 A at 500 V for power circuit conforming to IEC 60947 80 A at 500 V for power circuit conforming to NF C 63-110
Associated fuse rating	10 A gG for control circuit conforming to IEC 60947 10 A gG for control circuit conforming to VDE 0660 25 A gG at $\leq 440$ V for power circuit
Average impedance	3 mOhm at 50 Hz - Ith 20 A for power circuit
Inrush power in VA	30 VA at 20 °C
Hold-in power consumption in VA	4.5 VA at 20 °C 50/60 Hz
Operating time	10...20 ms between energisation of coil and closing of NO contact 10...20 ms coil de-energisation and NO opening 15...25 ms coil de-energisation and NC opening 5...15 ms coil energisation and NC opening

Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical durability	10000000 cycles
Operating rate	3600 cyc/h
Minimum switching current	5 mA for control circuit
Minimum switching voltage	17 V for control circuit
Insulation resistance	> 10 MOhm for control circuit
Height	58 mm
Width	45 mm
Depth	57 mm
Product weight	0.18 kg

## Environment

standards	BS 5424 IEC 60947 NF C 63-110 VDE 0660
product certifications	CSA GOST UL
IP degree of protection	IP2x conforming to VDE 0106
protective treatment	TC conforming to IEC 60068
ambient air temperature for operation	-25...50 °C
ambient air temperature for storage	-50...80 °C
operating altitude	2000 m without derating
fire resistance	850 °C conforming to IEC 60695-2-1
shock resistance	10 gn contactor closed 6 gn contactor opened
vibration resistance	2 gn 5...300 Hz contactor opened 4 gn 5...300 Hz contactor closed
heat dissipation	1.3 W at 50/60 Hz for control circuit

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0640 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available