



# PRODUCT DATA SHEET

## iL7





## PRODUCT DESCRIPTION

Long battery life meets light weight: With the Ledlenser iL7, weighing merely 232 g, you can work in Ex-Zone 2/22 areas for up to 37 hours. And you don't need to worry about sparks. Or if you're wearing work gloves. The extra large Magnetic Switch is even easy to operate with gloves.

- Magnetic Switch for easy operation with gloves and protective equipment
- Advanced Focus System for focusing
- Excellent price/performance ratio
- Light weight (232 g)
- Long battery life (up to 37 hours<sup>1</sup>)



### TECHNICAL DATA

Length defocused [mm]	161
Length focused [mm]	161
Head diameter [mm]	41
Tube diameter [mm]	41
Weight incl. batteries [g]	232
Weight without batteries [g]	164
Focus function	Yes
Head material	PC
Tube material	PC
Optic	Plastic lense (PMMA)
Cartridge	Yes

### POWER SUPPLY

Power source type	Battery
Battery quantity	3
Battery type	Alkaline
Battery description	Mignon (AA) 1.5V
Rechargeable	No

### EXPLOSION PROTECTION

ATEX Certificate	Baseefa18ATEX0070
IEC Ex Certificate	IECEx BAS18.0008
Ex marking	II 3G Ex ic IIC T4 Gc II 3D Ex ic IIIC T135°C Dc
Ex-Zone Gas	2
Gas Group	IIA, IIB, IIC
Temperature Class Gas	T4
Ex-Zone Dust	22
Dust Group	IIIA, IIIB, IIC
Temperature Class Dust	135 °C

### FURTHER SPECIFICATIONS

IP class	IP68
Drop test (drop height) [m]	1
Working temperature range [°C]	-20 to +40

### LIGHT FUNCTIONS

Low Power, Power

### LIGHT SOURCE

Amount LEDs	1
Color	White
Color temperature [K]	6000 to 8000
Color rendering index (CRI)	65

### LIGHT VALUES

	Boost	Power	Mid Power	Low Power
Light output <sup>1</sup> [lm]		340		70
Beam distance <sup>1</sup> [m]		165		80
Run time <sup>1</sup> [h]		7		37

### SWITCH

Magnetic Switch, Rotary Switch

### TECHNOLOGIES

Advanced Focus System<sup>3</sup>

iL7

## PACKAGING AND LOGISTICS



## PACKAGING INFORMATION

Type of packaging	Sleeve Box
Scope of delivery	1 set of batteries, Belt clip
Item No.	500838
Customs tariff number	85131000
Color	black
MSRP price (€)	69.90

## SINGLE PACKAGE

Dimensions W x H x D [cm]	22 x 7.4 x 8.4
Gross weight [g]	358
GTIN-13	4058205001304

## INNER CARTON

Unit	12
Dimensions W x D x H [cm]	46 x 23.5 x 19
Gross weight [g]	4606.5
GTIN-13	4058205001311

## EXPORT CARTON

Unit	24
Dimensions W x D x H [cm]	48 x 25.5 x 45
Gross weight [kg]	10.04
GTIN-13	4058205001328

The logo consists of the letters 'iL7' in a stylized font. The 'i' is black with a dot above it. The 'L' is black. The '7' is red. A horizontal line is positioned to the left of the 'i'.

## ACCESORIES

PRODUCT CATEGORY	ITEM NUMBER	PRODUCT NAME	MSRP
Fastenings / Brackets	500957	Intelligent Clip Type G	8.90 €
Color filter / Signal caps	500958	Signal Cone 42mm	6.90 €
Battery	500980	4x AA Alkaline Ionic	3.49 €



## PRODUCT SERIES

### The Ledlenser iL series

If you're working in explosive environments, safety is extremely important when it comes to electronics. Safety which is defined in the ATEX directives of the European Union. Lamps in the Ledlenser EX and iL series meet these standards in every respect.

Designed specifically for contact with explosive gases, vapors and dust in the best possible groups IIC and IIIC. Featuring dust and water protection, and certified to ATEX and IECEx. Yet both lines - in accordance with the ATEX workplace directives - are designed for different types of explosion hazards. The EX-series is suitable for areas where explosive atmospheres are regularly present (zones 0, 1, 20 or 21) and the iL-series for Zone 2/22. So you'll find the perfect lamp for any environment.

## FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

1) Measurements according to ANSI FL1 on the respective setting. Average values, in some cases, deviations by +/- 15 % may occur due to technical reasons. If no setting is explicitly indicated, the values refer to luminous flux (lumens/lm) and lighting range (meters/m) on the highest setting and to battery duration (hours/h) on the lowest setting. A boost function (if available) can be used several times, but only for short periods of time. If no setting is explicitly indicated, measurement is based on "energy saving mode."

3) EP Patent 1880139, US Patent 7,461,960

4) Warranty period of five years from the date of purchase, seven years if the product is registered online on our website. The warranty is valid worldwide and legal warranty rights also apply. It covers defects in materials and workmanship. For the proper functioning of rechargeable batteries a different warranty period of 24 months applies. Excluded from this warranty are the products of the "Solidline" series, Ledlenser K1 and Ledlenser K2. The warranty does not apply to defects in batteries, holsters, pouches, remote switches, color filters, imprints or surface coatings. The guarantor is Ledlenser GmbH & Co. KG, Kronenstr. 5 - 7, 42699 Solingen, Germany. More information: [ledlenser.com/warranty](http://ledlenser.com/warranty)