

### **INLINE HMI, TYPE 4**



### **INDUSTRY STANDARDS**

UL 508A Listed; Type 4, 12; File No. E61997 cUL Listed per CSA C22.2 No. 94; Type 4, 12; File No. E61997


NEMA/EEMAC Type 4, 12 CSA File Number 42186: Type 4, 12 IEC 60529, IP66

#### **APPLICATION**

Practical functionality is the signature feature of all INLINE HMI enclosures. With multiple options that allow for many different configurations, these enclosures are highly adaptable and useful in applications where a protective housing is required for small HMI devices.

#### **FINISH**

RAL 7035 textured light-gray polyester powder paint inside and out over pretreated surfaces. Optional panels are white.






### **SOLID-BACK BODY**

Solid-Back Body is 16 gauge steel with open front. Front is configured to install optional fixed bezel, deep-hinged window or fixed window. Panels or DIN rails mount on studs in the rear of the enclosure. Ground stud furnished. Drill points on enclosure mark location for pendant or pedestal mounting.

**BULLETIN: C3** 


Catalog Number	AxBxC mm/in.	Description	Product Weight (lb.)
LLB161612	166 x 160 x 102 6.54 x 6.30 x 4.00	Solid-Back Body	2.7
LLB252512	250 x 250 x 102 9.84 x 9.84 x 4.02	Solid-Back Body	5.0



## **REAR-ACCESS BODY**

Enclosure body is 16 gauge steel with rear-access door. Open front is configured to install optional fixed bezel, deep-hinged window or fixed window. Rear door, furnished with foam-in-place gasket and quarter-turn latch (standard slotted insert), accepts most INLINE door accessories. Ground stud furnished. Drill points on enclosure mark location for pendant or pedestal mounting.

**BULLETIN: C3** 



			Rear Door Opening	
Catalog Number	AxBxC mm/in.	Description	mm/in.	Product Weight (lb.)
LLBR161612	166 x 160 x 120	Rear Access Body	148 x 142	3.4
	6.54 x 6.30 x 4.72		5.82 x 5.58	
LLBR252512	250 x 250 x 120	Rear Access Body	232 x 232	5.7
	9.84 x 9.84 x 4.72		9.13 x 9.13	

nVent.com/H0FFMAN PH 763.422.2211 Spec-00333 | HMI (HUMAN-MACHINE INTERFACE) 2




# **FIXED-WINDOW KIT**



Aesthetic die-cast frame has .125-in.-thick clear polycarbonate window. Preassembled kit is secured to front opening of enclosure by mounting screws. Window frame caps conceal mounting screws. Frame has RAL 7035 light-gray textured polyester powder paint finish.

**BULLETIN: C3** 




Catalog Number	AxBxC mm/in.	Window Size M x N mm/in.	Product Weight (lb.)
LWF2525	250 x 250 x 17	220 X 200	2.7
	9.84 x 9.84 x 0.67	8.65 X 7.84	

#### **DEEP-HINGED WINDOW**



Clear molded polycarbonate window has a 31.8-mm (1.25-in.) clear space between enclosure front opening and window surface. Space also accommodates equipment mounted on optional front plate. Window kit is hinged on left side with a 140-degree door opening and a quarter-turn slotted latch. Includes mounting hardware for window and optional front plate. Die-cast backing plate has a black polyester powder finish. This kit can be used as an accessory window kit on other Hoffman enclosures.

**BULLETIN: C3** 



		Window Size M x N			
Catalog Number	AxBxC mm/in.	mm/in.	Accepts Front Plate	Product Weight (lb.)	
LWHD1616	166 x 160 x 41	139 x 112	LFP1616	1.5	
	6.54 x 6.30 x 1.64	5.47 x 4.43			
LWHD2525	250 x 250 x 41	223 x 202	LFP2525	2.8	
	9.84 x 9.84 x 1.64	8.78 x 7.97			

Purchase front plate separately.




### **FIXED HMI BEZEL**



Aesthetic die-cast bezel frame accepts front plate or plates with HMI cutout. Includes gasket and mounting hardware. Furnished frame caps conceal mounting screws. Bezel has RAL 7035 lightgray textured polyester powder paint finish.

**BULLETIN: C3** 



Catalog Number	AxBxC mm/in.	Window Size M x N mm/in.	Accepts Front Plate	Product Weight (lb.)
LBF1616	166 x 160 x 17 6.54 x 6.30 x 0.67	136 x 109 5.35 x 4.30	LFP1616	1.4
LBF2525	250 x 250 x 17 9.84 x 9.84 x 0.67	220 x 200 8.65 x 7.84	LFP2525	2.4

Purchase front plate separately.

#### FRONT PLATE, INLINE




Aluminum plate is .125-in. thick. Front Plate mounts to inside of bezel or deep-hinged window. Order blank or pre-cut for HMI. (Gasket and mounting hardware are included with bezel.) Hoffman can provide pre-configured front plates to meet your specific requirements. Contact your local Hoffman Sales Representative for more information.

BULLETIN: C3




Purchase deep window separately.



nVent.com/H0FFMAN PH 763.422.2211 Spec-00333 | HMI (HUMAN-MACHINE INTERFACE) 4




### **PANEL**




Panel is 12 gauge steel and fits solid back body enclosures only. Panels are painted white.

**BULLETIN: A54P** 

	D	E		
Catalog Number	mm/in.	mm/in.	Fits INLINE HMI Enclosure	Product Weight (lb.)
LP1515	131	131	LLB161612	0.7
	5.16	5.16		
LP2520	231	181	LLB252512	1.8
	0.00	T 10		



#### **DIN RAIL OR PANEL MOUNTING BRACKETS**




Brackets provide a mounting framework for installing DIN rails or a panel. Rails (or panel) attach to the brackets and the brackets are bolted directly to the enclosure. Brackets are offset to permit additional space in front of or behind mounted equipment. Brackets are plated 12 gauge steel.

#### **BULLETIN: A54Y**

Catalog Number	Fits INLINE HMI Enclosure	Product Weight (lb.)
LMK15	LLB161612	0.5
LMK20	LLB252512	0.6
LMK25	LLB252512	0.7


LMK20 fits horizontally. LMK25 fits vertically.


#### **DIN TYPE RAILS**



Rails furnish mounting surfaces for DIN3 mount snap-on devices. Rails attach vertically or horizontally to mounting brackets. Kit includes 4 rails, mounting hardware and installation instructions.

**BULLETIN: A54Y** 





87799016

Catalog Number	Fits INLINE HMI Enclosure	Product Weight (lb.)
LDR3P15	LLB161612	0.4
LDR3P20	LLB252512	0.5
LDR3P25	LLB252512	0.7

LDR3P20 fits horizontally. LDR3P25 fits vertically.

#### **LOCK INSERTS**



Lock Inserts can replace the standard slotted quarter-turn latch. Key included.

BULLETIN: A54SY, A54Y

Catalog Number	Description
LLKSM7	Square 7 mm, Chrome Finish
LLKSM7SS	Square 7 mm, Type 316L Stainless Steel
LLKSM8	Square 8 mm, Chrome Finish
LLKDB	Daimler Benz, Chrome Finish
LLKDBM3	Double bit 3 mm, Chrome Finish
LLKSS	Slotted screw, Chrome Finish



### **WING KNOB LATCH**




Wing Knob Latch can replace the standard slotted, quarter-turn latch on all hinged-cover and window-cover enclosures. Latch is black die-cast zinc. Includes two keys and installation instructions.

**BULLETIN: A54Y** 

Catalog Number	Product Weight
LLKWK	0.2 lb.

Reduces UL Type rating from 4 or 4X to 12.

## **MOUNTING BRACKET KIT, PLATED AND 316**



Kit is field-installable on all solid-back-body enclosures. Hardware included. Four brackets per kit.

### **BULLETIN: A54SY, A54Y**

Catalog Number	Description
LMFK	Plated steel mounting-bracket kit
LMFKSS	Type 316L stainless steel mounting-bracket kit

Use of LMFKSS recommended to maintain Type 4X rating.

## **GROUNDING KIT**



Grounding Kit provides means to attach a grounding conductor to the enclosure. Kit includes two insulated copper wires with a ring terminal at each end, all installation hardware and instructions.

#### **BULLETIN: A54Y**

Catalog Number	Product Weight
LLGK	0.2 lb.

nVent.com/H0FFMAN PH 763.422.2211 Spec-00333 I HMI (HUMAN-MACHINE INTERFACE) 6