DATASHEET - LS-11S/S



Position switch, 1N/O+1N/C, spring-rod head

Part no. LS-11S/S Catalog No. 266104 Eaton Catalog No. LS-11S/S EL-Nummer 4356031 (Norway)



Delivery program

Delivery program		
Basic function		Position switches
Part group reference		LS(M)
Product range		Spring-rod actuator
Degree of Protection		IP66, IP67
Features		Complete unit
Ambient temperature	°C	-25 - +70
Snap-action contact		Yes
Description		Not to be used as a safety position switch
Contacts		
N/O = Normally open		1 N/0
N/C = Normally closed		1 NC
Contact sequence		O-\frac{13}{14} \frac{1}{22}
Contact travel = Contact closed = Contact open		0° 13° 26° 21-22
Colour		
Enclosure covers		Yellow
Enclosure covers		
Housing		Insulated material
Connection type		Cage Clamp
Notes		Cage-Clamp is a registered trademark of Wago Kontakttechnik, 32432 Minden, Germany. Accessories for the Cage-Clamp terminals from Wago:power comb, gray, Wago Article No. 264-402
Rod length	mm	126

Technical data

				ı
15	ρı	16	ra	ı

Mounting position As required	Standards	IEC/EN 60947
Mounting position As required	Climatic proofing	Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-3
	Ambient temperature	°C -25 - +70
Degree of Protection IP66, IP67	Mounting position	As required
	Degree of Protection	IP66, IP67
Terminal capacities mm ²	Terminal capacities	mm ²
Solid mm ² 1 x (0.5 - 2.5)	Solid	mm ² 1 x (0.5 - 2.5)
Flexible with ferrule ${\rm mm}^2$ 1 x (0.5 - 1.5)	Flexible with ferrule	mm ² 1 x (0.5 - 1.5)

Contacts/switching capacity

our and our an			
Rated impulse withstand voltage	U_{imp}	V AC	4000
Rated insulation voltage	Ui	V	400
Overvoltage category/pollution degree			III/3
Rated operational current	le	Α	
AC-15			
24 V	l _e	Α	6
220 V 230 V 240 V	l _e	Α	6
380 V 400 V 415 V	Ie	Α	4
DC-13			
24 V	I _e	Α	3
110 V	le	Α	0.6
220 V	I _e	Α	0.3
Control circuit reliability			
at 24 V DC/5 mA	H _F	Fault probabilit	< 10 ⁻⁷ , < 1 fault in 107 operations ty
at 5 V DC/1 mA	H_{F}	Fault probabilit	< 10 ⁻⁶ , < 1 failure at 5 x 10 ⁶ operations ty
Supply frequency		Hz	max. 400
Short-circuit rating to IEC/EN 60947-5-1			
max. fuse		A gG/gL	6
Repetition accuracy		mm	0.15
Rated conditional short-circuit current		kA	1

Mechanical variables

Lifespan, mechanical	Operations	x 10 ⁶	8
Mechanical shock resistance (half-sinusoidal shock, 20 ms)			
Standard-action contact		g	25
Operating frequency	Operations/h		≦ 6000

Actuation

Mechanical		
Actuating force at beginning/end of stroke	N	1.0/8.0
Actuating torque of rotary drives	Nm	0.2

Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	In	Α	6
Heat dissipation per pole, current-dependent	P _{vid}	W	0.17
Equipment heat dissipation, current-dependent	P _{vid}	W	0
Static heat dissipation, non-current-dependent	P _{vs}	W	0
Heat dissipation capacity	P _{diss}	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	70
EC/EN 61439 design verification			

10.2 Strength of materials and parts	
10.2.2 Corrosion resistance	Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures	Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat	Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects	Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation	Meets the product standard's requirements.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9 Insulation properties	
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must observed.
10.13 Mechanical function	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 7.0


Technical data ETIM 7.0			
Sensors (EG000026) / End switch (EC000030)			
Electric engineering, automation, process control engineering / Binary sendecl@ss10.0.1-27-27-06-01 [AGZ382015])	sor technology, safety-	related s	sensor technology / Position switch / Position switch (Type 1)
Width sensor		mm	31
Diameter sensor		mm	0
Height of sensor		mm	61
Length of sensor		mm	33.5
Rated operation current le at AC-15, 24 V		Α	6
Rated operation current le at AC-15, 125 V		Α	6
Rated operation current le at AC-15, 230 V		Α	6
Rated operation current le at DC-13, 24 V		Α	3
Rated operation current le at DC-13, 125 V		Α	0.8
Rated operation current le at DC-13, 230 V		Α	0.3
Switching function			Quick-break switch
Switching function latching			No
Output electronic			No
Forced opening			No
Number of safety auxiliary contacts			1
Number of contacts as normally closed contact			1
Number of contacts as normally open contact			1
Number of contacts as change-over contact			0
Type of interface			None
Type of interface for safety communication			None
Construction type housing			Cuboid
Material housing			Plastic
Coating housing			Other
Type of control element			Spring-rod
Alignment of the control element			Other


Type of electric connection		Other
With status indication		No
Suitable for safety functions		Yes
Explosion safety category for gas		None
Explosion safety category for dust		None
Ambient temperature during operating	°C	25 - 70
Degree of protection (IP)		IP67
Degree of protection (NEMA)		4X

Approvals

Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14; CE marking
UL File No.	E29184
UL Category Control No.	NKCR
CSA File No.	12528
CSA Class No.	3211-03
North America Certification	UL listed, CSA certified
Degree of Protection	IEC: IP66, 67, UL/CSA Type 3R, 4X (indoor use only), 12, 13

Dimensions





Additional product information (links)

IL053001ZU LS-Titan position switch: basic device

IL053001ZU LS-Titan position switch: basic device

 $ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL053001ZU2018_06.pdf$