## **DATASHEET - LS-S11D**



## Position switch, 1N/O+1N/C, rounded plunger

Part no. LS-S11D Catalog No. 106791 Eaton Catalog No. LS-S11D EL-Nummer 0004315209 (Norway) Powering Business Worldwide\*

Delivery progran

Safety position switches  LSIMI	Delivery program		
Product range Degree of Protection Features Basic device, expandable Ambient temperature Contacts NO = Normally open NOtes NOtes Contact sequence  Contact trave = Contact closed = Contact open Contact trave = Contact closed = Contact open Enclosure covers Enclosure covers Enclosure covers Enclosure covers Enclosure covers  Housing  Rounded plunger 1P86, IP67 Basic device, expandable Basic dev	Basic function		
Degree of Protection Features Basic device, expandable Ambient temperature  COTACTS  N/O = Normally open N/C = Normally closed  Notes  Contact sequence  Contact sequence  Contact trave ■ = Contact closed = Contact open  Contact trave ■ = Contact closed = Contact open  Contact trave ■ = Contact closed = Contact open  Contact trave ■ = Contact closed = Contact open  Contact trave ■ = Contact closed = Contact open  Contact trave ■ = Contact closed = Contact open  Contact trave ■ = Contact closed = Contact open  Insulated material	Part group reference		LS(M)
Features Ambient temperature  **C	Product range		Rounded plunger
Ambient temperature  Contacts  N/O = Normally open N/C = Normally closed  Notes  Contact sequence  Contact travel = Contact closed = Contact open  Enclosure covers  Enclosure covers  Housing  Contact  Contact temperature  C	Degree of Protection		IP66, IP67
N/O = Normally open  N/C = Normally closed  Notes  Notes  Contact sequence  Contact travel ■ = Contact closed □ = Contact open  Positive opening (ZW)  Enclosure covers  Enclosure covers  Housing  I N/O  1 N/O  1 N/O  1 N/C  1 N/C  1 N/C  1 N/C  2 a safety function, by positive opening to IEC/EN 60947-5-1  1 Sold 1	Features		Basic device, expandable
N/O = Normally open  Notes  Notes  Contact sequence  Contact travel ■ = Contact closed □ = Contact open  Positive opening (ZW)  Enclosure covers  Enclosure covers  Housing  1 N/O  1 N/O  1 NC ⊕  1	Ambient temperature	°C	-25 - +70
Notes  Notes  Sequence  Contact sequence  Contact travel ■ = Contact closed = Contact open  Positive opening (ZW)  Enclosure covers  Enclosure covers  Enclosure covers  Enclosure covers  Insulated material	Contacts		
Notes  Description of the contact closed of the contact open  Solution and the contact closed of the contact open  Description opening (ZW)  Enclosure covers  Enclosure covers  Enclosure covers  Insulated material	N/O = Normally open		1 N/O
Contact sequence  Contact trave = Contact closed = Contact open  Contact trave = Contact closed = Contact open  Colour  Enclosure covers  Enclosure covers  Housing  Insulated material	N/C = Normally closed		1 NC →
Contact travel = Contact closed = Contact open    15-16	Notes		e safety function, by positive opening to IEC/EN 60947-5-1
Positive opening (ZW)  Positive opening (ZW)  Enclosure covers  Enclosure covers  Housing  Insulated material	Contact sequence		<u>~-√</u> /
Enclosure covers Enclosure covers  Housing  Yellow  Insulated material	Contact travel = Contact closed = Contact open		15-16 NC 27-28 NO
Enclosure covers Enclosure covers Housing  Yellow  Insulated material	Positive opening (ZW)		yes
Enclosure covers  Housing  Insulated material	Colour		
Housing Insulated material	Enclosure covers		Yellow
	Enclosure covers		
Connection type Screw terminal	Housing		Insulated material
	Connection type		Screw terminal

# Technical data General

donordi		
Standards		IEC/EN 60947
Climatic proofing		Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30
Ambient temperature	°C	-25 - +70
Mounting position		As required
Degree of Protection		IP66, IP67
Terminal capacities	$mm^2$	
Solid	$mm^2$	1 x (0.5 - 2.5)
Flexible with ferrule	$\text{mm}^2$	1 x (0.5 - 1.5)

0	to the later of	40.00
Contacts/	switchina'	capacity

Rated impulse withstand voltage	$U_{imp}$	V AC	4000	
---------------------------------	-----------	------	------	--

Rated insulation voltage	Ui	V	400
Overvoltage category/pollution degree			111/3
Rated operational current	I <sub>e</sub>	Α	
AC-15			
24 V	I <sub>e</sub>	Α	6
220 V 230 V 240 V	le	Α	6
380 V 400 V 415 V	le	Α	4
DC-13			
24 V	I <sub>e</sub>	Α	3
110 V	l <sub>e</sub>	Α	0.6
220 V	l <sub>e</sub>	Α	0.3
Control circuit reliability			
at 24 V DC/5 mA	H <sub>F</sub>	Fault probabilit	< 10 <sup>-7</sup> , < 1 fault in 107 operations
at 5 V DC/1 mA	H <sub>F</sub>	Fault probabilit	$< 10^{-6}$ , $< 1$ failure at $5 \times 10^{6}$ operations
Supply frequency		Hz	max. 400
Short-circuit rating to IEC/EN 60947-5-1			
max. fuse		A gG/gL	6
Repetition accuracy		mm	0.15
Rated conditional short-circuit current		kA	1
Mechanical variables			
Lifespan, mechanical	Operations	x 10 <sup>6</sup>	8
Contact temperature of roller head		°C	≦ 100
Mechanical shock resistance (half-sinusoidal shock, 20 ms)			
Standard-action contact		g	25
Operating frequency	Operations/h		≦ 6000
Actuation			
Mechanical			
Actuating force at beginning/end of stroke		N	1.0/8.0
Actuating torque of rotary drives		Nm	0.2
Max. operating speed with DIN cam		m/s	1/0.5
Notes			for angle of actuation $\alpha = 0^{\circ}/30^{\circ}$

## Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	In	Α	6
Heat dissipation per pole, current-dependent	$P_{\text{vid}}$	W	0.17
Equipment heat dissipation, current-dependent	P <sub>vid</sub>	W	0
Static heat dissipation, non-current-dependent	$P_{vs}$	W	0
Heat dissipation capacity	P <sub>diss</sub>	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	70
EC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat			Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects $$			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			Meets the product standard's requirements.
10.2.5 Lifting			Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			Meets the product standard's requirements.

10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9 Insulation properties	
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## **Technical data ETIM 7.0**


recimical data ettivi 7.0		
Sensors (EG000026) / End switch (EC000030)		
Electric engineering, automation, process control engineering / Binary sensor tech (ecl@ss10.0.1-27-27-06-01 [AGZ382015])	nnology, safety-relat	ted sensor technology / Position switch / Position switch (Type 1)
Width sensor	mm	31
Diameter sensor	mm	0
Height of sensor	mm	61
Length of sensor	mm	33.5
Rated operation current le at AC-15, 24 V	А	6
Rated operation current le at AC-15, 125 V	А	6
Rated operation current le at AC-15, 230 V	А	6
Rated operation current le at DC-13, 24 V	Α	3
Rated operation current le at DC-13, 125 V	Α	0.8
Rated operation current le at DC-13, 230 V	А	0.3
Switching function		Slow-action switch
Switching function latching		No
Output electronic		No
Forced opening		Yes
Number of safety auxiliary contacts		1
Number of contacts as normally closed contact		1
Number of contacts as normally open contact		1
Number of contacts as change-over contact		0
Type of interface		None
Type of interface for safety communication		None
Construction type housing		Cuboid
Material housing		Plastic
Coating housing		Other
Type of control element		Plunger
Alignment of the control element		Other
Type of electric connection		Other
With status indication		No
Suitable for safety functions		Yes
Explosion safety category for gas		None
Explosion safety category for dust		None
Ambient temperature during operating	°C	25 - 70
Degree of protection (IP)		IP67
Degree of protection (NEMA)		4X


# Approvals

Product Standards IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14; CE marking
--

UL File No.	E29184
UL Category Control No.	NKCR
CSA File No.	12528
CSA Class No.	3211-03
North America Certification	UL listed, CSA certified
Degree of Protection	IEC: IP66, 67, UL/CSA Type 3R, 4X (indoor use only), 12, 13

#### **Dimensions**





#### **Additional product information (links)**

IL053001ZU LS-Titan position switch: basic device

IL053001ZU LS-Titan position switch: basic device

 $ftp://ftp.moeller.net/DOCUMENTATION/AWA\_INSTRUCTIONS/IL053001ZU2018\_06.pdf$