## **DATASHEET - LS-S11/LB**



# Position switch, 1N/0+1N/C, roller lever long

Part no. LS-S11/LB
Catalog No. 106786
Eaton Catalog No. LS-S11-LB
EL-Nummer 0004315204
(Norway)



## Delivery program

Delivery program		
Basic function		Position switches Safety position switches
Part group reference		LS(M)
Product range		Roller lever
Degree of Protection		IP66, IP67
Features		Complete unit
Ambient temperature	°C	-25 - +70
Description		Large
Contacts		
N/O = Normally open		1 N/O
N/C = Normally closed		1 NC 🕒
Notes		= safety function, by positive opening to IEC/EN 60947-5-1
Contact sequence		0-13 121
Contact travel = Contact closed = Contact open		0 9.1 13.4 13-14 NO 21-22 NC $E_{W} = 9.6 \text{ mm}$
Positive opening (ZW)		yes
Colour		
Enclosure covers		Yellow
Enclosure covers		
Housing		Insulated material
Connection type		Screw terminal
$\textbf{Notes} \ \text{The operating head can be rotated at } 90^{\circ} \ \text{intervals to adapt to the specified approximation}$	ach direction.	

## **Technical data**

#### General

delleral		
Standards		IEC/EN 60947
Climatic proofing		Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30
Ambient temperature	°C	-25 - +70
Mounting position		As required
Degree of Protection		IP66, IP67
Terminal capacities	$mm^2$	

Solid		mm <sup>2</sup>	1 x (0.5 - 2.5)
Flexible with ferrule		$mm^2$	1 x (0.5 - 1.5)
Contacts/switching capacity			
Rated impulse withstand voltage	$U_{imp}$	V AC	4000
Rated insulation voltage	Ui	V	400
Overvoltage category/pollution degree			III/3
Rated operational current	I <sub>e</sub>	Α	
AC-15			
24 V	l <sub>e</sub>	Α	6
220 V 230 V 240 V	l <sub>e</sub>	Α	6
380 V 400 V 415 V	l <sub>e</sub>	Α	4
DC-13			
24 V	I <sub>e</sub>	Α	3
110 V	l <sub>e</sub>	Α	0.6
220 V	I <sub>e</sub>	Α	0.3
Control circuit reliability			
at 24 V DC/5 mA	H <sub>F</sub>	Fault probabili	
at 5 V DC/1 mA	$H_{F}$	Fault probabili	$< 10^{-6}$ , $< 1$ failure at 5 x $10^6$ operations
Supply frequency		Hz	max. 400
Short-circuit rating to IEC/EN 60947-5-1			
max. fuse		A gG/gL	6
Repetition accuracy		mm	0.15
Rated conditional short-circuit current		kA	1
Mechanical variables			
Lifespan, mechanical	Operations	x 10 <sup>6</sup>	8
Mechanical shock resistance (half-sinusoidal shock, 20 ms)			
Standard-action contact		g	25
Operating frequency	Operations/h		≦ 6000
Actuation			
Mechanical			
Actuating force at beginning/end of stroke		N	1.0/8.0
Actuating torque of rotary drives		Nm	0.2

# Design verification as per IEC/EN 61439

 $\ensuremath{\mathsf{Max}}.$  operating speed with DIN cam

Notes

Technical data for design verification			
Rated operational current for specified heat dissipation	In	Α	6
Heat dissipation per pole, current-dependent	$P_{\text{vid}}$	W	0.17
Equipment heat dissipation, current-dependent	P <sub>vid</sub>	W	0
Static heat dissipation, non-current-dependent	$P_{vs}$	W	0
Heat dissipation capacity	P <sub>diss</sub>	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	70
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat			Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects $$			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			Meets the product standard's requirements.
10.2.5 Lifting			Does not apply, since the entire switchgear needs to be evaluated.

1

for angle of actuation  $\alpha$  = 30°/45°

m/s

10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9 Insulation properties	
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.
10.10 Temperature rise	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

### **Technical data ETIM 7.0**


Sensors (EG000026) / End switch (EC000030)

Electric engineering, automation, process control engineering / Binary sensor technology, safety-related sensor technology / Position switch / Position switch (Type 1) (ecl@ss10.0.1-27-27-06-01 [AGZ382015]) Width sensor 31 Diameter sensor mm 0 Height of sensor 61 mm Length of sensor 33.5 mm Rated operation current le at AC-15, 24 V Α 6 Rated operation current le at AC-15, 125 V 6 Α Rated operation current le at AC-15, 230 V 6 Α Rated operation current le at DC-13, 24 V 3 Α Rated operation current le at DC-13, 125  $\rm V$ Α 0.8 Rated operation current le at DC-13, 230 V Α 0.3 Switching function Slow-action switch Switching function latching No Output electronic No Yes Forced opening Number of safety auxiliary contacts 1 Number of contacts as normally closed contact 1 Number of contacts as normally open contact Number of contacts as change-over contact 0 Type of interface None Type of interface for safety communication None Cuboid Construction type housing Plastic Material housing Coating housing **Other** Roller lever Type of control element Alignment of the control element Other Type of electric connection Other With status indication No Suitable for safety functions Yes Explosion safety category for gas None Explosion safety category for dust None Ambient temperature during operating °C 25 - 70 Degree of protection (IP) IP67


## **Approvals**

• •	
Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14; CE marking
UL File No.	E29184
UL Category Control No.	NKCR
CSA File No.	12528
CSA Class No.	3211-03
North America Certification	UL listed, CSA certified
Degree of Protection	IEC: IP66, 67, UL/CSA Type 3R, 4X (indoor use only), 12, 13

## **Dimensions**



- ① Tightening torque of cover screws: 0.8 Nm  $\pm$ 0.2 Nm ② only with LS (insulated version) ③ Fixing screws 2 x M4  $\geqq$  30 M<sub>A</sub> = 1.5 Nm



## **Additional product information (links)**

IL053001ZU LS-Titan position switch: basic device

IL053001ZU LS-Titan position switch: basic device

ftp://ftp.moeller.net/DOCUMENTATION/AWA\_INSTRUCTIONS/IL053001ZU2018\_06.pdf