旺 詮

Metal Alloy Low-Resistance Resistor Specifications


Document No.	IE-SP-022
Released Date	2011/10/19
Page No.	1/13

1 Scope:

This specification is applicable to lead free and halogen free for metal alloy low-resistance resistor by following products:

- LR1206 series
- LR2010 series
- LR2512 series
- LR2725 series
- LR2728 series
- LR4527 series

2 Explanation Of Part Numbers:



旺詮

Metal Alloy Low-Resistance Resistor Specifications

Document No.IE-SP-022Released Date2011/10/19Page No.2/13

3 Product Specifications:

	Number	Rated	Max.	Max.		Resist	ance Range	Operating
Туре	of Terminals	Power at 70℃	Rated Current	Overload	T.C.R (ppm / ℃)	D(± 0.5%)	F(± 1%) ∖ G(± 2%) J(± 5%)	
1 04000	2	0.5 W	22.36 A	44.72 A	1 ~ 4 mΩ ≦± 50 4.1 ~ 15 mΩ ≦± 25 15.1 ~ 50 mΩ ≦± 15		1 ~ 50 m Ω	
LR1206	2	1 W	31.62 A	63.25 A	1 ~ 4 mΩ \le ± 50 4.1 ~ 15 mΩ \le ± 25 15.1 ~ 50 mΩ \le ± 15	7 ~ 50 m Ω	1 ~ 50 mΩ	
LR2010	2	1 W	31.62 A	63.25 A	$\begin{array}{c} 1 \thicksim 3 \ m\Omega \leqq \pm \ 50 \\ 3.1 \thicksim 6.9 \ m\Omega \leqq \pm \ 25 \\ 7 \thicksim 100 \ m\Omega \leqq \pm \ 15 \end{array}$	7 ~ 100 m Ω	1 ~ 100 mΩ	
		1 W	44.72 A	100.00 A	$0.5 \sim 3 \text{ m}\Omega \leq \pm 50$			
		1.5 W	54.77 A	122.48 A	$3.1 \sim 6.9 \text{ m}\Omega \leq \pm 25$ 7 ~ 100 m $\Omega \leq \pm 15$	7 ~ 100 m Ω	0.5 ~ 100 mΩ	
LR2512	2	2 W	63.25 A	141.42 A	$\begin{array}{c} 0.5 \thicksim 3 \ \text{m}\Omega \leq \pm \ 50 \\ 3.1 \thicksim 6.9 \ \text{m}\Omega \leq \pm \ 25 \\ 7 \thicksim 75 \ \text{m}\Omega \leq \pm \ 15 \end{array}$	7 ~ 75 m Ω	0.5 ~ 75 m Ω	−55℃ ~ +170℃
		3 W	77.46 A	134.16 A	$\begin{array}{l} \textbf{0.5} \textbf{\sim} \textbf{2.5} \ \textbf{m} \Omega \leqq \pm \ \textbf{50} \\ \textbf{2.6} \textbf{\sim} \textbf{10} \ \textbf{m} \Omega \leqq \pm \ \textbf{25} \end{array}$	7 ~ 10 m Ω	0.5 ~ 10 mΩ	
LR2725	2	4 W	126.49 A	252.95 A	≦± 50		0.25 ~ 3 m Ω	
		3 W	27.39 A	47.43 A	4 ~ 7 mΩ≦± 25	4	100 0	
LR2728	2	3.5 W	29.58 A	51.23 A	7.1 ~100 m $\Omega \leq \pm$ 15			
	2	4 W	31.62 A	63.25 A	4 ~ 7 mΩ ≤± 25 7.1 ~50 mΩ ≤± 15	4 ~ 50 m Ω		
LR4527	2	3 W	77.5A	134A	≦± 50	7 ~ 120 m Ω	0.5 ~ 120 mΩ	
LI\4521	۷	5 W	100A	173A	<u>≧</u> 1 50	7 - 120 11132	0.5 ~ 120 1112	

Remark	IT' S NOT UNDER CONTROL FOR PDF FILE PLS NOTE THE VERSION STATED.	Issue Dep. DATA Center.
	Do not copy without permission	Series No. 60




旺詮

Metal Alloy Low-Resistance Resistor Specifications

Document No.IE-SP-022Released Date2011/10/19Page No.3/13

3.1 Power Derating Curve: Operating Temperature Range : - 55 ~+170 $^{\circ}$ For resistors operated in ambient temperatures above 70 $^{\circ}$, power rating shall be derated in accordance with figure below.



3.2 Rating Current:

1

Rated Current: The resistor shall have a DC continuous working current or a RMS(Root Mean Square). AC continuous working current at commercial-line frequency and wave form corresponding to the power rating, as determined from the following:

$=\sqrt{P/R}$	I= Rating current (A)
$-\sqrt{1}$	P= Rating power (w)
	R= Nominal resistance (Ω)


Remark	IT' S NOT UNDER CONTROL FOR PDF FILE PLS NOTE THE VERSION STATED.	Issue Dep. DATA Center.
	Do not copy without permission	Series No. 60

RALEC 旺 詮

Metal Alloy Low-Resistance Resistor Specifications

Document No.IE-SP-022Released Date2011/10/19Page No.4/13

4 Dimensions:



TVDE	Power	Resistance		Dim	ensions (m	ım)	
TYPE	Rating (W)	Range (mΩ)	L	W	Н	T1	T2
LR1206	0.5 1	1~50	3.200± 0.254	1.600± 0.254	0.645± 0.254	0.508± 0.254	/
LR2010	1	1.0~3 3.1~100	5.080± 0.254	2.540± 0.254	0.787± 0.254 0.645± 0.254	1.295± 0.254 0.787± 0.254	. /
	1 1.5	0.5~4 4.1~75 75.1~100			0.645± 0.254 0.645± 0.254 0.645± 0.254	1.880± 0.254 1.118± 0.254 0.868± 0.254	
LR2512	2	0.5~4 4.1~75	6.248± 0.254	3.302± 0.254	0.787± 0.254 0.645± 0.254	1.880± 0.254 1.118± 0.254	
	3	0.5 0.6~2.9 4.1~10 3~4		0.787± 0.254	1.880± 0.254 1.118± 0.254 1.676± 0.254		
LR2725	4	0.25 \ 0.5 1 1.5 2 2.5 3	6.807± 0.254	6.452± 0.254	0.991± 0.254 1.092± 0.254 0.991± 0.254 0.889± 0.254	2.159± 0.254 1.803± 0.254 1.651± 0.254 1.295± 0.254	
LR2728	3 3.5 4	4~100	6.706± 0.254	7.188± 0.254	0.991± 0.254	1.143± 0.254	
LR4527	3 5	0.5 0.6~5.0 5.1~120	11.430± 0.254	6.850± 0.254	1.500± 0.254	3.215±0.254 1.815±0.254	3.215±0.254 0.965±0.254

Remark	IT' S NOT UNDER CONTROL FOR PDF FILE PLS NOTE THE VERSION STATED.	Issue Dep. DATA Center.
	Do not copy without permission	Series No. 60

旺 詮

Metal Alloy Low-Resistance Resistor Specifications

Document No.IE-SP-022Released Date2011/10/19Page No.5/13

5 Reliability Performance Test 5.1 Electrical Performance Test

Item		Conditions	Specifications
Temperature Coefficient of Resistance	TCR (ppm/°C) = $\frac{(1)}{R1}$ R1: Resistance at roor R2: Resistance at +15 T1: Room temperature T2: Temperature at +1	n temperature 0℃	Refer to Paragraph 3. general specifications
	Refer to JIS-C5201-1	4.8	
Short Time Overload		5 seconds and release the load for n measure its resistance variance ion refer to below)	
	Туре	Overload	damage.
	LR1206-0.5W	4 times of rated power	
	LR1206-1W	4 times of rated power	
	LR2010-1W	4 times of rated power	
	LR2512-1W	5 times of rated power	
	LR2512-1.5W	5 times of rated power	
	LR2512-2W	5 times of rated power	
	LR2512-3W	3 times of rated power	
	LR2725-4W	4 times of rated power	
	LR2728-3W	3 times of rated power	
	LR2728-3.5W	3 times of rated power	
	LR2728-4W	4 times of rated power	
	LR4527-3W	3 times of rated power	
	LR4527-5W	3 times of rated power	
	Refer to JIS-C5201-1	4.13	
Insulation Resistance	Put the resistor in the for 60secs then me	fixture, add 100 VDC in + ,- terminal easured the insulation resistance nd insulating enclosure or between naterial.	
Dielectric		minute, and Limit surge current 50	No short or burned on the
Withstand	mA (max.)	4.7	appearance.
Voltage	Refer to JIS-C5201-1	4.7	

Remark	IT' S NOT UNDER CONTROL FOR PDF FILE PLS NOTE THE VERSION STATED.	Issue Dep. DATA Center.
	Do not copy without permission	Series No. 60

旺 詮

Metal Alloy Low-Resistance Resistor Specifications

Document No.IE-SP-022Released Date2011/10/19Page No.6/13

5.2 Mechanical Performance Test

Item	Conditions	Specifications
Solderability	Add flux into tested resistors, immersion into solder bath in temperature $245\pm$ 5°C for $3\pm$ 0.5 secs. Refer to JIS-C5201-1 4.17	Solder coverage over 95%
Resistance to Solvent	The tested resistor be immersed into isopropyl alcohol of $20\sim25^{\circ}$ C for 60 secs, then the resistor is left in the room for 48 hrs. Refer to JIS-C5201-1 4.29	$\leq \pm$ 0.5% No evidence of mechanical damage.
Resistance to Soldering Heat	The tested resistor be immersed 25 mm/sec into molten solder of $260 \pm 5^{\circ}$ C for 10 ± 1 secs. Then the resistor is left in the room for 1 hour, and measured its resistance variance rate. Refer to JIS-C5201-1 4.18	$\leq \pm 0.5\%$ No evidence of mechanical damage.
Vibration	The resistor shall be mounted by its terminal leads to the supporting terminals on the solid table. The entire frequency range :from 10 Hz to 55 Hz and return to 10 Hz, shall be transferred in 1 min. Amplitude : 1.5 mm This motion shall be applied for a period of 4 hours in each 3 mutually perpendicular directions (a total of 12 hr) Refer to JIS-C5201-1 4.22	$\leq \pm$ 0.5% No evidence of mechanical damage.

Remark	IT' S NOT UNDER CONTROL FOR PDF FILE PLS NOTE THE VERSION STATED.	Issue Dep. DATA Center.
	Do not copy without permission	Series No. 60

旺 詮


Metal Alloy Low-Resistance Resistor Specifications


Document No.IE-SP-022Released Date2011/10/19Page No.7/13

5.3 Environmental Test

Item	Condition	ns	Specifications
High Temperature Exposure	Put tested resistor in chamber under temperature $170\pm$ 5°C for 1000 hours. Then leaving the tested resistor in room temperature for 60 minutes , and measure its resistance variance rate. Refer to JIS-C5201-1 4.23.2		$\leq \pm$ 1.0% No evidence of mechanical damage.
Low Temperature Exposure	Put the tested resistor in chamber under temperature -55± 2°C for 1000 hours. Then leaving the tested resistor in room temperature for 60 minutes, and measure its resistance variance rate. Refer to JIS-C5201-1 4.23.4		$\leq \pm 0.5\%$ No evidence of mechanical damage.
Tamperature cycling (Rapid Tamperature Change)	Put the tested resistor in the cha tamperature cycling which show shall be repeated 1000 times co leaving the tested resistor in the 60 minutes, and measure its res Lowest Temperature Highest Temperature Temperature-retaining time Refer to JIS-C5201-1 4.19	n in the following table onsecutively. Then room temperature for	$\leq \pm$ 0.5% No evidence of mechanical damage.
Moisture Resistance (Climatic Sequence)	Put the tested resistor in chamb cycles of damp heat . Each one steps 1 to 7 (Figure 1). Then lea in room temperature for 24 hr, a resistance variance rate. Refer to MIL-STD 202 Method 1	of which consists of the aving the tested resistor and measure its	$\leq \pm 0.5\%$ No evidence of mechanical damage.
Moisture Life	Put the tested resistor in chamber under $85\pm 5^{\circ}$ C/85 $\pm 5^{\circ}$ RH with 10% bias and load the rated voltage for 90 minutes on, 30 minutes off, total 1000 hours. Then leaving the tested resistor in room temperature for 60 minutes, and measure its resistance variance rate. Refer to JIS-C5201-1 4.24		≤± 0.5% No evidence of mechanical damage.
Load Life	Put the tested resistor in chamb 70± 2°C and load the rated volt 30 minutes off, total 1000 hours tested resistor in room tempera and measure its resistance vari Refer to JIS-C5201-1 4.25	age for 90 minutes on, s. Then leaving the ture for 60 minutes,	$ \stackrel{\leq \pm}{=} 1.0\% \\ \stackrel{\leq \pm}{=} 2.0\% (4527-3W \& 4527-5W) \\ \hline \text{No evidence of mechanical damage.} $

Remark	IT' S NOT UNDER CONTROL FOR PDF FILE PLS NOTE THE VERSION STATED.	Issue Dep. DATA Center.
	Do not copy without permission	Series No. 60





7 Recommend Land Pattern :

а

b

Unit : mm Land Pattern Dimensions Maximum TYPE **Power Rating** Resistance а b i (Watts) Range (m Ω) LR1206 0.5 & 1.0 1.0~50.0 1.60 2.18 1.00 1.0~3.0 2.89 2.92 1.22 LR2010 1.0 2.29 2.92 2.41 3.1~100.0 а 0.5~4.0 3.05 3.68 1.27 LR2512 1.0 & 1.5 4.1~100.0 3.18 2.11 3.68 LR2512 0.5~4.0 3.05 3.68 1.27 2.0 4.1~75.0 2.11 3.68 3.18 0.50 3.05 3.68 1.27 0.6~2.9 & 3.00 LR2512 3.0 2.19 3.68 4.1~10.0 3.0 ~ 4.0 2.79 3.68 1.80 LR2725 4.0 0.25~3.0 3.18 6.86 1.32 LR2728 3.0 \$ 3.5 & 4.0 4.0~100.0 2.75 7.82 3.51

0.5~5.0

5.1~120

4.80

3.40

8.74

8.74


5.51

8.31


Remark	IT' S NOT UNDER CONTROL FOR PDF FILE PLS NOTE THE VERSION STATED.	Issue Dep. DATA Center.
	Do not copy without permission	Series No. 60

3.0 & 5.0

LR4527



RALE	C Metal Alloy Low-Resistance	Document No.	IE-SP-022					
旺言		Released Date	2011/10/19					
		Page No.	11/13					
«	$\langle EX \rangle$ Marking \rightarrow 5m25=5.25 m Ω (greater than 4 m Ω)							
	5m25							
K	EX» Marking \rightarrow 25m5=25.5 m Ω (greater than 4 m Ω)							
	25m5							
-	R2725							
«	EX» Marking \rightarrow 0m25=0.25 m Ω (for 0.25 m Ω only)							
	0m25							
«	EX $\$ Marking \rightarrow 2m50 = 2.5 m Ω (for 2.5 m Ω only)							
	2m50							
«	EX》Marking \rightarrow R003=3 m Ω (for 1 m Ω \sim 2 m Ω and 3 m Ω or	ıly)						
	R 0 0 3							
Demo		Issue De	p. DATA Center.					
Remark	IT'S NOT UNDER CONTROL FOR PDF FILE PLS NOTE THE VERSION STATED.							
	Do not copy without permission	Series N	o. 60					




旺詮

Metal Alloy Low-Resistance Resistor Specifications

Document No.IE-SP-022Released Date2011/10/19Page No.13/13

9 Taping Specifications

9.1 Tape Dimension:




<u>unit : mm</u>

DIM TYPE	А	В	w	E	F	T1	T2	Р	P0	10x P0	P1
LR1206	3.48± 0.10	1.83± 0.10	8.0± 0.15	1.75± 0.10	3.5± 0.10	0.90 ± 0.10	0.20 ± 0.05	4.0± 0.10	4.0± 0.10	40.0± 0.20	2.0± 0.10
LR2010	5.45± 0.10	2.90± 0.10	12.0± 0.15	1.75± 0.10	5.5± 0.10	1.10 ± 0.10	0.23 ± 0.05	4.0± 0.10	4.0± 0.10	40.0± 0.20	2.0± 0.10
LR2512	6.74± 0.10	3.90± 0.10	12.0± 0.15	1.75± 0.10	5.5± 0.10	1.08 ± 0.10	0.24 ± 0.05	8.0± 0.10	4.0± 0.10	40.0± 0.20	2.0± 0.10
LR2725	7.15± 0.10	6.75± 0.10	12.0± 0.15	1.75± 0.10	5.5± 0.10	1.70 ± 0.10	0.25 ± 0.05	8.0± 0.10	4.0± 0.10	40.0± 0.20	2.0± 0.10
LR2728	7.15± 0.10	7.70± 0.10	12.0± 0.15	1.75± 0.10	5.5± 0.10	1.20 ± 0.10	0.25 ± 0.05	12.0± 0.10	4.0± 0.10	40.0± 0.20	2.0± 0.10
LR4527	11.80± 0.10	7.20± 0.10	24.0± 0.15	1.75± 0.10	11.5± 0.10	1.70 ± 0.10	0.30 ± 0.10	12.0± 0.10	4.0± 0.10	40.0± 0.20	2.0± 0.10

9.2 Packaging Quantity:

	Tana	Pack	aging Quantity (po	cs/reel)				
Туре	Tape Width	Emboss Plastic Type						
	width	4 mm Pitch	8 mm Pitch	12 mm Pitch				
LR1206	8 mm	4000 pcs						
LR2010	12 mm	2000 pcs						
LR2512	12 mm		2000 pcs					
LR2725	12 mm		1000 pcs					
LR2728	12 mm			1000 pcs				
LR4527	24 mm			500 pcs				

9.3 Reel Dimensions:



	Ont int								
-	Reel Type/ Tape	W	м	A	В	С	D		
	7" reel for 8 mm tape	12.0 ± 0.5		2.0 ± 0.5	13.2 ± 0.5		60.0 ± 0.5		
	7" reel for 12 mm tape	16.2 ± 0.5	178 ± 1.0	2.5 ± 0.5	13.5 ± 0.5	17.7 ± 0.5	60.0 ± 0.5		
-	7" reel for 24 mm tape	24.4 +2/-0		2.0 ± 0.5	13.2 ± 0.5		60.0 ± 0.5		

10 Attachments

10.1 Document Revise Record

(QA-QR-027)

Remark	IT'S NOT UNDER CONTROL FOR PDF FILE PLS NOTE THE VERSION STATED.	Issue Dep. DATA C	DATA Center.
	Do not copy without permission	Series No.	60

Unit : mm