### DATASHEET - LS-XNG-ZBZ



Compensating actuator, flat

Part no.LS-XNG-ZBZCatalog No.106834Eaton Catalog No.LS-XNG-ZBZEL-Nummer0004356187(Norway)



### **Delivery program**

Basic function	actuators
Part group reference	LSZBZ/X
Function	Flat compensating actuator
Description	With increased tolerance in closing direction Stainless steel
For use with	doors that do not close precisely
Notes for combination with LSZBZ/X basic devices	

Technical data			
General			
Standards			IEC/EN 60947
Climatic proofing			Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30
Mounting position			As required
Terminal capacities		mm <sup>2</sup>	
Solid		mm <sup>2</sup>	1 x (0.75 - 2.5) 2 x (0.75 - 1.5)
Flexible with ferrule		mm <sup>2</sup>	1 x (0.5 - 1.5) 2 x (0.5 - 1.5)
Contacts/switching capacity			
Rated impulse withstand voltage	U <sub>imp</sub>	V AC	4000
Rated insulation voltage	Ui	V	400
Overvoltage category/pollution degree			111/3
Rated operational current	Ι <sub>e</sub>	А	
AC-15			
24 V	le	А	6
220 V 230 V 240 V	I <sub>e</sub>	A	6
380 V 400 V 415 V	Ι <sub>e</sub>	A	4
DC-13			
24 V	I <sub>e</sub>	А	3
110 V	Ι <sub>e</sub>	А	0.8
220 V	I <sub>e</sub>	А	0.3
Supply frequency		Hz	max. 400
Short-circuit rating to IEC/EN 60947-5-1			
max. fuse		A gG/gL	6
Repetition accuracy		mm	0.02
Mechanical variables			
Mechanical shock resistance (half-sinusoidal shock, 20 ms)			
Standard-action contact		g	10
Operating frequency	Operations/h		≦ 800
Actuation			
Mechanical			
Mechanical holding force acc. to GS-ET-19 (04/2004)			
XG, XW, XNG		Ν	1700
XWA, XFG, XF		Ν	1600
XNW		Ν	1200
Electromechanical			
For magnet			

Power consumption		
at 120 V AC	VA	8
at 24 V DC	W	8
Pick-up and drop-out values	x U <sub>s</sub>	0.85 - 1.1
Magnet duty factor	% ED	100

# Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	In	А	0
Heat dissipation per pole, current-dependent	P <sub>vid</sub>	W	0
Equipment heat dissipation, current-dependent	P <sub>vid</sub>	W	0
Static heat dissipation, non-current-dependent	P <sub>vs</sub>	W	0
Heat dissipation capacity	P <sub>diss</sub>	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	40
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat			Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			Please enquire
10.2.5 Lifting			Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			Meets the product standard's requirements.
10.5 Protection against electric shock			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			Is the panel builder's responsibility.
10.8 Connections for external conductors			Is the panel builder's responsibility.
10.9 Insulation properties			
10.9.2 Power-frequency electric strength			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			Is the panel builder's responsibility.
10.10 Temperature rise			Not applicable.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

#### **Technical data ETIM 7.0**

Sensors (EG000026) / Actuator for position switch with separate actuator (EC001487)


Electric engineering, automation, process control engineering / Binary sensor technology, safety-related sensor technology / Position switch / Actuator for position switch with separate actuator (ecl@ss10.0.1-27-27-06-05 [BAA078012])

Actuator with horizontal mounting


Model

Approvals	
Product Standards	IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14; CE marking
UL File No.	E29184
UL Category Control No.	NKCR
CSA File No.	12528
CSA Class No.	3211-03
North America Certification	UL listed, CSA certified





Fixing only allowed with M5 fixing screw and washer according to DIN EN ISO 7093 1 Distance to device head = 0.1  $\dots$  3.0 mm



# Additional product information (links)

#### IL05208005Z (AWA1310-2354) Safety position switch

IL05208005Z (AWA1310-2354) Safety position ftp://ftp.moeller.net/D0CUMENTATION/AWA\_INSTRUCTIONS/IL05208005Z2018\_11.pdf switch